

# SMT3000C

APC Smart-UPS, Line Interactive, 3kVA, Tower, 120V, 8 NEMA 5-15R+2 NEMA 5-20R outlets, SmartConnect Port+SmartSlot, AVR, LCD



## Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

## Main

Main Input Voltage	120 V
Input voltage	110 V 125 V
Output voltage	120 V
Output voltage	110 V 125 V
Rated power in W	2700 W
Rated power in VA	2880 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L5-30P
Output connection type	8 NEMA 5-15R 2 NEMA 5-20R
Cable length	1.83 M
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	Smart UPS signalling RS-232 cable USB cable

## Complementary

Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use
------------------	---

## Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1

Battery life	3...5 Year(S)
Battery charger power	271 W rated

## General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No

## Physical

Colour	Black
Height	43.5 Cm
Width	19.6 Cm
Depth	54.4 Cm
Net weight	52.73 Kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

## Input

Input voltage limits	75...154 V adjustable 82...144 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2880 VA
Maximum configurable power in W	2700 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product certifications	cULus[RETURN]ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

## Environmental

Acoustic level	45 dBA
Heat dissipation	275 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

## Communications & Management

Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies-by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

## Surge Protection and Filtering

Surge energy rate	530 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	55.9 Cm
Package 1 Width	76.2 Cm
Package 1 Length	38.1 Cm
Package 1 Weight	60.91 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
ENERGY STAR®	<a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go-to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Product Life Status : **Commercialised**