

SMT3000IC

APC Smart-UPS, Line Interactive, 3kVA,
Tower, 230V, 8x IEC C13+2x IEC C19 outlets,
SmartConnect Port+SmartSlot, AVR, LCD



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Input voltage	220 V 240 V
Output voltage	230 V
Output voltage	220 V 240 V
Rated power in W	2700 W
Rated power in VA	3000 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number of rack unit	0U
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	USB cable

Complementary

Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use
------------------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery charger power	271 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No

Physical

Colour	Black
Height	43.5 Cm
Width	19.7 Cm
Depth	54.4 Cm
Net weight	52.5 Kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE[RETURN]EAC[RETURN]RCM[RETURN]VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	53 dBA
Heat dissipation	375 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C

Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies-by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	365 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	69.9 Cm
Package 1 Width	76.2 Cm
Package 1 Length	38.1 Cm
Package 1 Weight	63.7 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Logistical informations

Country of origin	PH
-------------------	----

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Product Life Status : **Commercialised**