



Galaxy VS

Increased availability. Reduced operating costs.
First-class power protection for critical infrastructure.

20–150 kW (480 V)
10–75 kW (208 V)



se.com/gvs

Schneider
Electric

Maximize your availability; minimize your total cost of ownership

Galaxy VS is a highly efficient, modular, simple-to-deploy 20–150 kW (480 V)/10–75 kW (208 V) 3-phase uninterruptible power supply (UPS) that delivers top performance to edge, small, and medium data centers, as well as critical infrastructure in commercial and industrial facilities.

With highly efficient patented technologies and modular architecture, Galaxy VS maximizes your availability while minimizing your total cost of ownership.

Galaxy VS meets your internal redundancy needs with N+1 power modules to ensure your load remains protected. This multiplies by 10 the system's availability without extra footprint.

Its flexible battery options—from long-life Galaxy Lithium-ion cabinets to classic VRLA with smart modules—provide optimized runtimes and predictable performance for critical loads.

EcoStruxure™ connectivity gives you real-time visibility into UPS health and performance from anywhere, enabling peace of mind and proactive management. Combined with Live Swap capability, superior scalability, and compact design, Galaxy VS is the ideal backbone for today's resilient and future-ready infrastructure.

Well-suited for a wide range of data center and industrial applications



Information technology and commercial buildings

- Edge, small, and medium data centers
- Computer rooms
- Retail/office space
- Manufacturing facilities



Healthcare

- Radiology and imaging equipment
- Operating rooms and Intensive Care Units
- Emergency power systems



Oil & gas

- Refining
- Petrochemicals
- Gas processing control
- Well pumps



Transportation

- Marine (DNV, BV)
- Lighting
- Air traffic control
- Security
- Signaling and communication systems



Minerals, Metals & Mining

- Furnace process control
- Glass plants
- Emergency lighting



Power & Grid

- Thermal plants
- Generator protection
- Hydro turbine control
- Wind farm monitoring



Next-level transparency for better-informed product choices. Learn more about the Environmental Data Program at: se.com/www/en/about-us/sustainability/environmental-data-program

Galaxy VS also complies with these standards¹:

- Emergency lighting: UL® 924, CSA® 22.2 NO. 141-15
- TAA, BAA, and BABA compliant UPS (in the United States)²



¹ Model-dependent.

² Contact your local representative for availability.

³ Consult your local representative for more information about configuration requirements, including accessory kits.



99% efficient in patented eConversion mode

Recover your initial investment within two-to-three years through energy savings.¹



New patented hybrid technology

Provides up to 97% efficiency in double conversion mode.

Electricity savings in full protection mode at every load level.



Compact design. Optimized footprint

High-density technology and full-front access make Galaxy VS a footprint saver well-suited for confined spaces.



Maximum availability thanks to modular architecture

Critical system components built as modules for faster serviceability and fault tolerance. N+1 redundancy, scalability, and Live Swap options available.



Battery flexibility, including Lithium-ion batteries²

Increase availability and reduce TCO with long-life, intelligent energy storage.



EcoStruxure IT

Anytime, anywhere monitoring and service support via smartphone app³.



Leading performance

Robust and flexible design, ideal for demanding environments at maximum performance




Flexibility and performance

- **Unity Power Factor (PF=1)** ensures right-sized protection for IT needs
- High overload capability and wide input tolerance ($\pm 15\%$) for demanding applications
- Seamless integration with single or dual mains support
- Flexible DC bus and right-sized batteries for optimized run time



Higher availability: maximum uptime, reduced risk

- One extra power module for **N+1 internal redundancy** keeps your load protected and multiplies system availability by 10 with no extra footprint
- Optimized uptime with wide input tolerance window ($\pm 15\%$)
- With **Live Swap***, it is simple and fast to add, replace, or remove power modules
- N+0 or N+1 module-level redundancy
- N+0 or N+1 system-level redundancy (parallel up to 4 UPSs)



Reliable power for IT and non-IT environments

- Robust, fault-tolerant design ensures continuous protection in critical circumstances
- Designed to perform in dusty environments with its high-quality air filter and IP20 rating (optional **IP52 kit** available for select models)
- Withstands **104 °F operating temperature** without derating (122 °F with derating)
- Suited for humid environments thanks to **conformal coating**
- **Seismic certified** (with option kit)
- Maximum short circuit rating: 65 kA
- Exceeds industry standards on electromagnetic protection due to EMC Level C2
- **Faster battery charging** capabilities restore back-up time two-to-three times faster compared to industry standards
- Operates at **high elevation** with no derating up to 1000 m (3000 m with derating)
- Models with **halogen-free** power cables available

* model dependent

Premium protection and sustainability


eConversion: an unbeatable combination of power quality and high efficiency



Sustainably reduce your operating costs

Protect power to your load, reduce your total cost of ownership and electricity consumption, and meet your sustainability goals with up to 99% efficient, Class 1-compliant eConversion mode for Galaxy V-series UPSs, the recommended operating mode for your Galaxy V-series UPS.*

- By operating at up to **99% efficiency**, the electricity savings in eConversion within 10 years typically equals **3x the price of the UPS**.
- The inverter operates continuously, protecting the load with **no transfer time**. eConversion performance has been certified with the same IEC 62040-3 **Class 1** rating as double conversion mode.
- eConversion mode recharges batteries and provides power factor correction and harmonics compensation, making it a **versatile solution for IT and non-IT loads**.
- Since its launch in 2014, eConversion has been successfully deployed all over the world. Join thousands of customers who use it daily to protect their critical loads.




Calculate your savings

See how much you can save with Galaxy VS in eConversion mode. Use our quick calculator to compare energy costs, operating expenses, and CO₂ reduction versus double conversion mode.

Scan the QR code with your phone camera, or [click here](#) to access the calculator from the Schneider Electric Data Center Trade Off Tools™ Web page.



[Learn more about eConversion](#)



*Model dependent; based on a market electricity price: \$0.15 /kWh. The annual electricity savings are calculated by comparing the UPS efficiency in eConversion mode vs. double conversion mode.

Meets your needs in multiple environments




	Galaxy VS for external batteries	Galaxy VS with internal smart battery modules		
208 V	10–75 kW	10 kW	10–25 kW	10–50 kW
480 V	20–150 kW	20 kW	20–50 kW	20–100 kW
N+1 redundancy option*	Yes	No	No	Yes
Scalability option*	Yes	No	No	No
Dimensions	59"H x 20.5"W	59"H x 13.8"W	59"H x 20.5"W	78"H x 20.5"W
Battery type	External. Compatible with Lithium-ion and lead-acid (VRLA)	7Ah (VRLA)	9Ah (VRLA) Standard or long life	9Ah (VRLA) Standard or long life
Battery strings in UPS (maximum)	–	2	4	5
Ingress protection level	IP21 (IP52 options)	IP20	IP20	IP20
Special features:	Large cabling section provides convenient access, connection, and installation. Models with Live Swap capability and scalability available.	Models with Live Swap capability available.	Compatible with external modular battery cabinets (up to 6 battery strings). Models with Live Swap capability available.	Compatible with external modular battery cabinets (up to 9 battery strings). Models with Live Swap capability available.

Future-proof your data center

Galaxy VS UPS with optional scalability empower you to right-size your power protection to today's load requirement, then change UPS capacity as your load requirements evolve over time.

- Add 20 kW and 50 kW power modules, combined as needed
- Galaxy VS UPS self-detects the addition of a new power module and automatically updates its configuration setting

In addition, Galaxy VS UPS models with third-party verified Live Swap maximize uptime, availability, and power continuity by enabling you to swap out power modules quickly, with no scheduled downtime.



* See technical specifications table for details

Options and accessories

Galaxy VS is available with a full range of options and accessories that ensure the best performance in any environment.

Batteries



Galaxy Lithium-ion battery cabinets



Classic battery cabinets



Modular battery cabinets

Maintenance bypasses



Maintenance bypass cabinet



Wall mount maintenance bypass panel



Maintenance bypass cabinet with transformer

Accessories

- Seismic kit
- Air filter kit
- Parallel communications kit
- NEMA® 2-hole kit**
- Kirk key
- IP52/NEMA®12 kits**
- Mounting skid for marine or industrial applications
- Remote alarm panel
- Smart modular battery string
- Smart modular high capacity battery string
- Smart long-life high capacity battery string
- Galaxy VS Live Swap upgrade kit
- 20 kW UPS with 480 V:400 V transformer (tolerates high peak loads up to 80 kW)
- Fire Marshal Kit (Japan)



IP52 / NEMA®12 kit for UPS**



IP52 / NEMA®12 kit for battery cabinet**



Mounting skid for marine or industrial applications

* Contact your local representative for availability.

** Model dependent; contact your local representative for order details.

Faster installation and serviceability

Quick to install and fits everywhere, thanks to its compact design


- Lightweight, small footprint, with rolling casters
- Ships with everything you need — Network Management Card (NMC), modbus, single and dual mains, air filters, and eight dry contacts
- Precise and reliable battery configuration, thanks to predefined battery parameters
- Set up a simplified 1+1 parallel configuration using the built-in internal maintenance bypass breaker, or use an external maintenance bypass panel to configure parallel installations for capacity or redundancy
- Supports a common battery bank for parallel installations
- Supports installation with NEMA® 2-hole lugs

Simple to maintain and fast to service, thanks to its modular architecture

- Fast mean time to repair, thanks to swappable power, static switch, battery, and intelligence modules
- Full-front access for simple and fast connection and service (Galaxy VS for external batteries)
- Reduces risk of human error and load drop, and enhances employee protection:
 - For Galaxy VS UPSs with the Live Swap option, it is simple and fast to add, replace, or remove a power module while the Galaxy VS UPS is online and fully operational, increasing protection for your employees
 - Galaxy VS self-detects the new power module and automatically updates its configuration settings, delivering more uptime and convenience
 - If needed, the easy and intuitive guided maintenance bypass transfer sequence on the display helps you easily transfer to and from maintenance bypass and monitors the system breaker status

Modular design benefits

- 1 Intelligence module**
“System brain” contains critical control and signal wire interfaces
- 2 Scalability option**
Add new power module anytime as your load evolves
- 3 Power modules**
N+1 redundancy, Live Swap, slide in/slide out modules with rear connectors. Includes fan box for simple replacement. Superb core performances (PF=1, high-density, high-efficiency) and fault-tolerant design
- 4 Static switch module**
Replaceable without installing an external maintenance bypass solution
- 5 Internal maintenance bypass**
Simplifies service operations and reduces risk of error
- 6 Smart modular battery strings**
Integrates smart battery modules in the UPS cabinet, conserving footprint and increasing availability with battery monitoring, additional battery strings, and fast runtime expansion with self-configuring modules





Galaxy VS for external batteries



Galaxy VS with internal batteries

Flexible, intelligent energy storage

Galaxy VS is available with a full range of energy storage options that ensure the best performance in any environment and meet a wide variety of site requirements.



ModBC #1	GVSMODBC6		
#6		✓	23°C CSB 9Ah
#5		✓	27°C CSB 9Ah
#4		✓	27°C CSB 9Ah
#3		✓	26°C CSB 9Ah
#2		✓	28°C CSB 9Ah
#1		✓	27°C CSB 9Ah

Improved availability, including long-life options

- **Increased availability:** Four smart battery modules form one smart modular battery string. All smart battery modules support the load so no individual battery is a single point of failure
- **Reduced Mean Time To Repair (MTTR):** Replace a smart battery module in just a few minutes

Accurate anytime replacement

- **Simple:** Push-in and plug; unplug and pull-out
- **Safety first:** Touchproof connectors
- **Self-configuring:** The UPS automatically detects the presence and type of batteries so the battery configuration is updated accurately

Battery monitoring included

- **Sensors:** Each smart battery module contains two temperature sensors and a battery identification device for self-configuration
- **Runtime:** The estimate on the display interface updates when smart battery modules are removed or installed
- **Quick status on display:** Use the UPS display to quickly identify and replace an inoperative smart battery module

Flexible, high-density energy storage

- **Right-sizing:** Easily increase runtime by adding battery modules or installing battery cabinets
- **High density:** Integrate batteries in the UPS to reduce footprint. No need for service clearance between battery rows

Long-life Galaxy Lithium-ion batteries

As a first mover with a vast installed base, Schneider Electric has developed its own Galaxy Lithium-ion battery solution that also delivers these benefits:

- **Double** your battery life compared with any VRLA battery, optimizing TCO and achieving sustainability targets
- Recharge **2-3x faster** than VRLA solutions
- High temperature tolerance
- Simplify and speed up installation with our internal power supply
- Enhance battery safety with three levels of battery management system (BMS)

for Lithium-ion / VRLA
battery comparison

Classic VRLA batteries

- Quickly install the battery cabinet next to the UPS
- Compact footprint



Visibility and peace of mind

Secure Network Management Card System*

Bolster your cybersecurity strategy with firmware updates

As cybersecurity is a leading concern for business interruptions, the **Secure Network Management Card (NMC) System** is our commitment to deliver secure products, utilizing secure development processes, and reliable update management reducing exposure to cybersecurity attacks.



The Schneider Electric Network Management Card is independently certified to the IEC 62443-4-2 standard by TÜV Rheinland. Additionally, our development processes are certified to both IEC and ISA Security Standards.

Updating your NMC firmware matters



Monitoring and alarming

Remote monitoring and visibility across IT infrastructure is mission critical, because it reduces the risk of unexpected issues and downtime.



Wherever-you-go visibility

The Schneider Electric Network Management Card enables essential and secure remote monitoring and management of your Galaxy VS.



Preventative management

Connecting your devices will improve the availability, resiliency, and efficiency of your power infrastructure systems and the IT workloads they support.



Ongoing security compliance

More and more cybersecurity breaches are linked to neglected firmware. Our new Secure NMC System will help you:

- Reduce exposure to attack and minimize downtime—protect your connected devices with the latest security updates.
- Achieve consistent compliance—protect your business with the only NMC firmware independently certified to the highest cybersecurity compliance level (IEC 62443-4-2).
- Never become out of date—during commissioning of your Galaxy VS and during maintenance activities, Schneider Electric qualified services representative update the NMC firmware as defined in all applicable field advisories and field modifications.

Learn more at se.com/secure-nmc

* Requires an Advantage Plan service contract or EcoCare for 3-Phase UPS membership with on-site maintenance; contact your Schneider Electric representative for availability.

EcoStruxure IT

EcoStruxure IT enables resilient, secure, and sustainable data centers and IT environments

Schneider Electric's comprehensive Data Center Infrastructure Management (DCIM) solution, EcoStruxure IT, ensures business continuity by enabling secure monitoring, management, insights, planning, and modeling—whether from a single IT rack to hyper-scale IT—on-premises, in the cloud, and at the edge.

Easy visibility

Monitoring and management software streamlines data center device management:




EcoStruxure IT Expert provides you a hands-on approach with cloud-based monitoring software that synthesizes and analyzes performance and alert data into proactive recommendations and enables wherever-you-go visibility from any device. [Try it now.](#)



EcoStruxure Data Center Expert is a scalable end-to-end on-premise monitoring software that collects, organizes, and distributes critical device information, providing a comprehensive view of your company-wide, multi-vendor physical infrastructure.

24/7 peace of mind

Digital services proactively monitor your critical devices:



EcoStruxure Asset Advisor* for secure power and cooling provides you a hands-off approach with 24/7 remote monitoring service by the Schneider Electric Connected Services Hub experts. We monitor and troubleshoot, you relax.

Operations, optimized

Planning and modeling software transforms data into performance insights:



EcoStruxure IT Advisor is a data center infrastructure planning and modeling solution that provides Data Center Managers in large enterprises and colocation data centers with full insights into their infrastructure to improve profitability, sustainability, and resiliency.

Comprehensive on-site services

Start-up service: included with UPS

- Commission the installation in accordance with manufacturer's recommendations. Ensure optimal system performance from Day 1

Schneider Electric-certified installation services

- Expert configuration of your equipment for optimal performance and reliability

Maintenance services

- Ensure proper care of your mission-critical applications
- Preventive maintenance and response time upgrades, where available

Flexible service plans/ on-site extended warranty


- Hassle-free system maintenance
- Improve uptime at a predictable cost

Technical specifications

Galaxy VS	480 V	208/220 V
Topology	On-line double conversion	
Nominal power (kW)	20–150 kW (parallel up to 600 kW)	10–75 kW (parallel up to 300 kW)
Key features		
Scalability option	50–150 kW	25–75 kW
N+1 redundancy option	20–100 kW N+1	10–50 kW N+1
Modular elements	Power modules with Live Swap, static switch module, smart battery modules, intelligence module	
Display	Color touch screen, 4.3 inches, status LED, mimic on display	
Communication	Network management card included with ethernet (SNMP) and modbus. 8 dry contacts (4 inputs, 4 outputs)	
Maintenance bypass	Internal maintenance bypass. Optional maintenance bypass panel/cabinet	
Parallel capability	Simplified 1+1 parallel (for redundancy); Up to 4 UPSs in parallel for capacity or redundancy	
Efficiency		
Double conversion mode	Up to 97%	Up to 95.5%
ECO mode	Up to 99%	
eConversion mode	Up to 99%	
Input		
Nominal input voltage	200/208/220 V, 480 V (600 V with transformer*)	
Input voltage range (phase to phase)	+/-15%	
Single mains/dual mains	Single mains as standard. Easily converted to dual mains	
Input frequency	40–70 Hz	
Input power factor	0.99 for load greater than 50% 0.95 for load greater than 25%	
Maximum short-circuit rating	65 kA	
Backfeed protection	Included	
Output		
Nominal output voltages	200/208/220 V, 480 V (600 V with transformer*)	
Load power factor	PF=1 (0.7 leading to 0.7 lagging without derating)	
Voltage regulation	+/- 1%	
Frequency	50/60 Hz +/-0.1% free running	
Overload	1 min @ 150%; 10 min @ 125%	
Output THDU on linear load	10–150 kW 480V UPS	10–75 kW 208 V UPS for external batteries, 10–50 kW 208 V UPS with up to 4 internal battery strings: <2% 10–50 kW 208 V UPS with up to 5 internal battery strings: <1%
Battery type	VRLA, Li-ion	
Nominal battery voltage, UPS for external batteries	20–40 kW, 80 kW: 384–576 V DC 50 kW, 100 kW: 480–576 V DC 60 kW: 432–576 V DC	384–480 V DC
Nominal battery voltage, UPS with internal batteries	480 V DC	
Charging power	Charging power in % of output power at 0-40% load: 80% Charging power in % of output power at 100% load: 20%	
Environment		
Acoustic noise, UPS for external batteries	54 dB (70% load) / 61 dB (100% load)	57 dB (70% load) / 65 dB (100% load)
Acoustic noise, UPS with internal batteries	49–65 dB, depending on load percentage and model	
Dust protection	Air filter included. Conformal coated boards	
Seismic	With optional kit. OSHPD tested	
Environmental	Product Environmental Profile (PEP), RoHS, REACH	

* Available in Canada

Specifications can be subject to change.



To learn more about the Galaxy VS UPS and EcoStruxure IT DCIM, contact your Schneider Electric representative or visit se.com/gvs

About Schneider Electric: Schneider Electric is a global energy technology leader, driving efficiency and sustainability by electrifying, automating, and digitalizing industries, businesses, and homes. Its technologies enable buildings, data centers, factories, infrastructure, and grids to operate as open, interconnected ecosystems, enhancing performance, resilience, and sustainability. The portfolio includes intelligent devices, software-defined architectures, AI-powered systems, digital services, and expert advisory. With 160,000 employees and one million partners in over 100 countries, Schneider Electric is consistently ranked among the world's most sustainable companies.

www.se.com

Schneider Electric SE
800 Federal Street
Andover, MA 01810 USA
se.com