



UK DECLARATION OF CONFORMITY

We : MANUFACTURER
Schneider Electric Industries SAS
35 rue Joseph Monier
Rueil Malmaison 92500 – France

UK REPRESENTATIVE
Schneider Electric Limited
Stafford Park 5
Telford, TF3 3BL - United Kingdom

Hereby declare under our sole responsibility that the product:

Trademark	Schneider Electric
Product, Type	Altivar HVAC ATH200 & dedicated options
List of references and options	See next pages

are in conformity with the requirements of the following regulations and conformity was checked in accordance with the following standards.

Regulation	Designated standard / Notified body reference
Electrical Equipment (Safety) Regulations SI 2016 No. 1101	EN 61800-5-1:2007 EN 61800-5-1:2007 + A1:2017 EN 61800-5-1:2007 + A11:2021 Adjustable speed electrical power drive systems – Part 5-1: Safety requirements – Electrical, thermal and energy. Other standard considered: (IEC 61800-5-1:2016)
The Electromagnetic Compatibility Regulations SI 2016 No. 1091	EN 61800-3:2004 EN 61800-3:2004/A1:2012 Adjustable speed electrical power drive systems – part 3: EMC requirements and specific test methods. Other standard considered: (IEC 61800-3:2017)
The Ecodesign for Energy-Related Products Regulations SI 2010 No 2617	EN 61800-9-2:2017 Ecodesign for power drive systems, motor starters, power electronics and their driven applications - Energy efficiency indicators for power drive systems and motor starters (IEC 61800-9-2:2017)
The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 SI 2012 No. 3032	EN IEC 63000:2018 Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances. Specific offer compliance information about RoHS are publicized on se.com

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions and to accepted rules of the art.

This declaration becomes invalid in the case of any modification to the products not authorized by Schneider Electric.

Compliance with the ATEX, Machinery & EMC Regulation will require the application of the ATEX guide, Safety guide and EMC guide giving requirements, details and advices for installation of products used.

The guides are available on <http://www.se.com>

The undersigned also agrees to transmit relevant information in response to a reasoned request from any adequate way by a national authority.

Person in charge of technical documentation:

Sylvain Ballet, Schneider Toshiba Inverter Europe, rue André Blanchet, 27120 Pacy/Eure – France.

Issued at Telford - United Kingdom (Representative): 2025-09-12

Signed by:

 A578D60923D7459
David WILLIAMS
 VP Marketing UK&I
 Zone UK & Ireland
 Customer Satisfaction & Quality - Vice President



UK DECLARATION OF CONFORMITY

List of references:

One phase 200V to 240Vac

Reference (1) IP20 models	Range
ATH230U04M2	0.37KW
ATH230U06M2	0.55KW
ATH230U07M2	0.75KW
ATH230U11M2	1.1KW
ATH230U15M2	1.5KW
ATH230U22M2	2.2KW

(1) may be followed by 1 to 3 characters.

Three phases 200V to 240Vac

Reference (1) IP20 models	Range
ATH230U04M3	0.37KW
ATH230U06M3	0.55KW
ATH230U07M3	0.75KW
ATH230U11M3	1.1KW
ATH230U15M3	1.5KW
ATH230U22M3	2.2KW
ATH230U30M3	3KW
ATH230U40M3	4KW
ATH230U55M3	5.5KW
ATH230U75M3	7.5KW
ATH230D11M3	11KW
ATH230D15M3	15KW

(1) may be followed by 1 to 3 characters.

Compliance with EMC directive will require the installation of all system components (ATH230●●●M3C + Additional EMC input filters) and the application of the EMC guide which gives requirements, details and advices for installation of products used.

Reference	
VW3A31402	Additional EMC input filters
VW3A31404	Additional EMC input filters
VW3A31406	Additional EMC input filters
VW3A31407	Additional EMC input filters
VW3A31408	Additional EMC input filters



UK DECLARATION OF CONFORMITY

Three phase 380V to 480Vac

Reference (1) IP20 models	Range
ATH230U06N4	0.55KW
ATH230U07N4	0.75KW
ATH230U11N4	1.1KW
ATH230U15N4	1.5KW
ATH230U22N4	2.2KW
ATH230U30N4	3KW
ATH230U40N4	4KW
ATH230U55N4	5.5KW
ATH230U75N4	7.5KW
ATH230D11N4	11KW
ATH230D15N4	15KW
ATH230D18N4	18.5kW
ATH230D22N4	22kW

(1) may be followed by 1 to 3 characters.

Three phase 525V to 600Vac

Reference (1)	Range
ATH230U15S6	1.5KW
ATH230U22S6	2.2KW
ATH230U40S6	4KW
ATH230U55S6	5.5KW
ATH230U75S6	7.5KW
ATH230D11S6	11KW
ATH230D15S6	15KW

(1) may be followed by 1 to 3 characters.



UK DECLARATION OF CONFORMITY

List of options and accessories:

Commercial reference	Short Description
VW3A1111	GRAPHIC DISPLAY TERMINAL
VW3A1112	DOOR MOUNTING KIT FOR GRAPHIC KEYPAD
VW3A1115	Remote Kit web server Ethernet
VW3A36201	I/O control card for ATV320 Compact Ctrl
VW3A3600	Communication adapter card
VW3A3601	ETHERCAT DAISY CHAIN COMMUNICATION CARD
VW3A3607	ELECTRONIC OPTION CARD PROFIBUS ATV32 LX
VW3A3608	ELECTRONIC OPTION CARD CANOPEN 2XRJ45 AT
VW3A3609	ELECTRONIC CARD DEVICENET ATV32
VW3A3616	ELECTRONIC OPTION CARD ETHERNET TCP/IP A
VW3A3618	ELECTRONIC OPTION CARD CANOPEN SUBD9 ATV
VW3A3619	ATV32 POWERLINK FIELDBUS MODULE
VW3A3620	INTERFACE CARD PTI ATV32
VW3A3627	ATV32 profinet communication card
VW3A7701 to VW3A7736	BRAKING RESISTOR IP20 or IP00
VW3A7603R07 to VW3A7608R07	BRAKING RESISTOR IP65 0,75M
VW3A7603R30 to VW3A7608R30	BRAKING RESISTOR IP65 3M
VZ1L004M010	Single INDUCTOR
VZ1L007UM50	Single INDUCTOR
VZ1L018UM20	Single INDUCTOR
VW3A4551 to VW3A4556	AC CHOKES
VW3A4420 to VW3A4462	EMC INPUT FILTER
VW3A31401 to VW3A31409	EMC INPUT FILTER
VW3A31410	EMC INPUT FILTER FOR Size 6
VW3A3726	BACnet IP for ATH200