



IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
Produit

Uninterruptible power supply

Name and address of the applicant
Nom et adresse du demandeur

American Power Conversion Corp.
85 Rangeway Road Building 2, NORTH BILLERICA MA 01862
USA

Name and address of the manufacturer
Nom et adresse du fabricant

American Power Conversion Corp.
85 Rangeway Road Building 2, NORTH BILLERICA MA 01862
USA

Name and address of the factory
Nom et adresse de l'usine

American Power Conversion Corporation b.v
Breaffy Road, CASTLEBAR CO. MAYO
IRELAND

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Input / Output: refer to model matrix

Trademark (if any)
Marque de fabrique (si elle existe)

APC

Model / Type Ref.
Ref. De type

SYAF - series, refer to model matrix

Additional information (if necessary)
Information complémentaire (si nécessaire)

Class I, WMT

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

PUBLICATION	EDITION
IEC 60950(ed.3);corrigendum	


As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

1924400-3335-0033

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

VDE VERBAND DER ELEKTROTECHNIK
ELEKTRONIK INFORMATIONSTECHNIK e.V.
VDE Prüf- und Zertifizierungsinstitut
VDE Testing and Certification Institute
Zertifizierungsstelle / Certification

Date:
2004-11-15


Signature:

SYMMETRA – LX MATRIX

VDE Reference Number: 1924400-3335-0033

Frame: SYAF8KI, SYAF8KRMI, SYAF16KI, SYAF16KRMI, SYAF16KXR9I, SYAF20KRMI.

Input: AC 220/230/240, 1 ϕ + N + GND, 50-60 Hz, 100A

AC 380/400/415, 3 ϕ + N + GND, 50-60 Hz, 100A

Output: AC 220/230/240, 1 ϕ + N + GND, 50-60 Hz, 100A


Total Output Power: 8 kVA, 5.6 kW (SYAF8K units)
16 kVA, 11.2 kW (SYAF16K units)
20 kVA, 14 kW (SYAF20K units)

Model SKU	Power Module SYPM4KI	Intelligence Module SYMIM5	Battery Module SYBT5
SYAF8KI	3	2	2
SYAF8KRMI	3	2	2
SYAF16KI	5	2	4
SYAF16KRMI	5	2	4
SYAF16KXR9I	5	2	13
SYAF20KRMI	5	2	4

PDU Panels:

SYPD10

OM6362



i.A. *[Signature]*
12.11.2004