



Ref. Certif. No.

**US-35456-M1-UL**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product Accessory, Automatic Transfer Switch - Single Phase for use in certified ITE

Name and address of the applicant SCHNEIDER ELECTRIC IT CORPORATION  
70 MECHANIC ST FOXBORO, MA 02035  
UNITED STATES

Name and address of the manufacturer SCHNEIDER ELECTRIC IT CORPORATION  
70 MECHANIC ST FOXBORO, MA 02035  
UNITED STATES

Name and address of the factory DANAM PHILIPPINES INC  
BLK 15, PHASE 3, LOT 1-A  
PEZA ROSARIO, CAVITE, 4106  
PHILIPPINES

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics AP4421#:  
230V, 10A, 50/60Hz  
10A PER BANK 10A MAX  
 Additional Information on page 2 through 4

Trademark (if any) APC by Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref. AP4421#, AP4422#, AP4423#, AP4424#, AP4425#  
 Additional Information on page 2

Additional information (if necessary may also be reported on page 2)  
The report was revised to include technical modifications.  
 Additional Information on page 4

A sample of the product was tested and found to be in conformity with IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate E177299-A6009-CB-1 issued on 2021-09-16

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2021-09-16  
Original Issue Date: 2020-03-19

Signature: Jolanta M. Wroblewska



Ref. Certif. No.

**US-35456-M1-UL**

**Additional Model Detail(s):**

AP4421#, AP4422#, AP4423#, AP4424#, AP4425#, AP4430#, AP4431#, AP4432#, AP4433#, AP4434#, AP4450#, AP4450#J, AP4452#, AP4452#J, AP4453#,

Where “#” = any letter to denote alternate NMC PWB and alternate outlet PWB construction

**Additional Ratings:**

AP4422#:

230V, 16A, 50/60Hz  
16A OUTPUT MAX

AP4423#:

INPUT:  
220-230 VAC, 16A, 50/60Hz  
UL OUTPUT:  
230 VAC  
10A PER C13 BANK 16A MAX  
16A MAX PER C19  
KOREA OUTPUT  
220 VAC  
10A PER C13 BANK 16A MAX  
16A MAX C19

AP4424#:

INPUT:  
220-230 VAC, 32A, 50/60Hz,  
UL OUTPUT:  
230 VAC  
10A PER C13 BANK 16A MAX  
16A MAX C19  
KOREA OUTPUT:  
220 VAC  
10A PER C13 BANK 16A MAX  
16A MAX C19

AP4425#:

230 VAC, 32A, 50/60Hz

AP4430#:

UL  
INPUT:  
208 VAC, 16A, 50/60Hz

OUTPUT:  
208 VAC 16A, 50/60Hz

JAPAN

INPUT:  
200 VAC, 20A, 50/60Hz

OUTPUT:  
200 VAC, 20A, 50/60Hz

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Signature:

Jolanta M. Wroblewska

Date: 2021-09-16

Original Issue Date: 2020-03-19



Ref. Certif. No.

**US-35456-M1-UL**

**Additional Ratings:**

AP4431#:

INPUT:

208 VAC. 1PH 24A, 50/60Hz,

OUTPUT:

208 VAC. 1PH 24A, 50/60 Hz

AP4432#:

UL

INPUT:

208 VAC, 24A, 50/60Hz

OUTPUT:

208 VAC, 20A MAX PER BANK

JAPAN

INPUT:

200 VAC, 30A, 50/60Hz

OUTPUT:

200 VAC, 20A MAX PER BANK

AP4433#:

INPUT:

208 VAC. 12A, 50/60Hz

OUTPUT:

208 VAC. 10A PER OUTLET 50/60Hz

10A PER C13 BANK 12A MAX

AP4434#:

INPUT:

208 VAC. 16A, 50/60Hz

OUTPUT:

208 VAC. 16A 50/60 Hz

12A MAX PER C13 BANK

AP4450#:

UL

INPUT:

120 VAC. 12A, 50/60 Hz

OUTPUT:

120 VAC.

12A PER OUTLET 50/60 Hz

AP4450#J

JAPAN

INPUT:

100 VAC. 15A, 50/60Hz

OUTPUT:

100 VAC. 15A PER OUTLET, 50/60Hz

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Signature:

Jolanta M. Wroblewska

Date: 2021-09-16

Original Issue Date: 2020-03-19



Ref. Certif. No.

**US-35456-M1-UL**

**Additional Ratings:**

AP4452#:

INPUT:

120 VAC. 16A, 50/60Hz

OUTPUT:

120 VAC. 16A PER OUTLET 50/60Hz

AP4452#J:

INPUT:

100 VAC. 20A, 50/60Hz

OUTPUT:

100 VAC. 15A PER OUTLET 50/60Hz

AP4453#:

INPUT:

120 VAC. 24A, 50/60Hz

OUTPUT:

120 VAC. 16A MAX PER BANK

**Additionally evaluated to:**

EN 62368-1:2014, EN 62368-1:2014/A11:2017, National Differences specified in the CB Test Report.

**Summary of Modifications:**

The original report was modified to include the following changes/additions:

Amendment 2 (Technical):


- Added alternate outlet PCB PWB, alternate logic board, display board, and NMC board.
- Added “#” designator to all of the models in report to designate these alternate components in the end product.
- The Japanese variant of model AP4450 was assigned a designator “J” to distinguish input ratings and now reads as AP4450#J.

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Signature:   
Jolanta M. Wroblewska

Date: 2021-09-16

Original Issue Date: 2020-03-19