




Ref. Certif. No.

US-36671-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Accessory, Power Distribution Unit - Single and Poly phase, for use in certified ITE.
Name and address of the applicant	SCHNEIDER ELECTRIC IT CORPORATION, FKA APC AMERICAN POWER CONVERSION 132 FAIRGROUNDS RD, PO BOX 278 WEST KINGSTON, RI 02892 USA
Name and address of the manufacturer	SCHNEIDER ELECTRIC IT CORPORATION, FKA APC AMERICAN POWER CONVERSION 132 FAIRGROUNDS RD, PO BOX 278 WEST KINGSTON, RI 02892 USA
Name and address of the factory	EAST INDIA TECHNOLOGIES PVT. LTD. SURVEY NO. 17, KAMMANAHALLI VILLAGE BANNERGHATTA RD BANGALORE KARNATAKA 560076 INDIA
<i>Note: When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Pages 2 through 9 APC by Schneider Electric
Trademark / Brand (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Basic Models AP6002A, AP6003A, AP6007A, AP6009A, See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E177299-A6016-CB-1 issued on 2020-10-15

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-10-15
Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Model Details:

Basic Models (Cont'd):

AP6015A, AP6020A, AP6031A, AP6032A, AP6038A, AP6120A, AP7541, AP7567A, AP9559, AP9562, AP9565, AP9567, AP9568, AP9570, AP9571A, AP9571AX459, AP9572

Smart Models

AP7800B, AP7811B, AP7820B, AP7821B, AP7900B, AP7911B, AP7920B, AP7921B

Basic Models

AP7530J (PSE ONLY), AP7532J (PSE ONLY), AP7526 (EMEA ONLY), AP7551 (EMEA ONLY), AP7552 (EMEA ONLY), AP7553 (EMEA ONLY), AP7554 (EMEA ONLY), AP7555A (EMEA ONLY), AP7557 (EMEA ONLY)

Smart Models:

AP7802BJ (PSE ONLY), AP7902BJ (PSE ONLY), AP7822B (EMEA ONLY), AP7850B (EMEA ONLY), AP7922B (EMEA ONLY), AP7950B (EMEA ONLY)

Factories:

SCHNEIDER ELECTRIC IT BUSINESS INDIA PVT LTD
PLOT NO 73 SURVEY NO. 103, 2ND PHASE JIGANI INDUSTRIAL AREA BANGALORE KARNATAKA 562106
INDIA

SGS TEKNIKS MANUFACTURING PRIVATE LIMITED

PLOT NO 211, JIGANI-BOMMASANDRA LINK ROAD INDUSTRIAL AREA, JIGANI, BANGALORE, BENGALURU
(BANGALORE) RURAL KARNATAKA 560106
INDIA

Ratings:

Basic Models

AP6002A

Input: 200-240 VAC, 1~, 24A, 50/60Hz

Output: 200-240 VAC, 1~

12A PER OUTLET / 15A PER GROUP

16A PER OUTLET, 16A PER BANK, 24A TOTAL

PSE

Input: 200-240 VAC, 1~30A, 50/60Hz

Output: 200-240 VAC, 1~

15A PER OUTLET

20A PER OUTLET

AP6003A

UL-EU

Input: 100-240 VAC, 1~, 16A, 50/60 Hz

Output: 100-240 VAC, 1~, 16A

C13: 10A PER OUTLET

Input: 100-240 VAC, 1~, 16A, 50/60Hz

Output: 100-240 VAC, 1~

MAX CURRENT: 16A

C13: 12A PER OUTLET

PSE

Input: 100-240 VAC, 1~, 20A, 50/60Hz

Output: 100-240 VAC 1~

MAX CURRENT: 20A

C13: 15A PER OUTLET

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska

Ratings:

AP6007A

Input: 200-240 VAC, 50/60Hz, 45A

Output: 200-240 VAC, 16A PER BANK, 45A MAX

C19: 16A PER OUTLET, 16A PER GROUP

C13: 12A PER OUTLET, 16A PER GROUP

UL-EU

Input: 200-240 VAC, 50/60Hz, 32A

Output: 200-240 VAC, 16A PER BANK, 32A MAX

C19: 13A PER OUTLET, 16A PER GROUP

C13: 10A PER OUTLET, 16A PER GROUP

AP6009A

Input: 200-240 VAC, 50/60Hz, 32A

Output: 200-240 VAC, 32A MAX, 16A PER BANK

C19: 16A PER OUTLET, 16A PER GROUP

C13: 10A PER OUTLET, 16A PER GROUP

AP6015A

Input: 100-240 VAC, 1~ 12A, 50/60Hz

Output: 100-240 VAC, 1~ 12A MAX

C13: 12A PER OUTLET

UL-EU

Input: 200-240 VAC, 1~, 10A, 50/60Hz

Output: 200-240 VAC, 1~, 10A MAX

C13: 10A PER OUTLET

AP6020A

Input: 100-240 VAC, 1~, 16A, 50/60Hz

Output: 100-240 VAC 1~, 16A MAX

C13: 12A PER OUTLET

PSE

Input: 100-240 VAC, 1~, 20A, 50/60Hz

Output: 100-240 VAC 1~, 20A MAX

C13: 15A PER OUTLET

UL-EU

Input: 200-240 VAC, 1~, 16A, 50/60Hz

Output: 200-240 VAC, 1~, 16A MAX

C13: 10A PER OUTLET

AP6031A

Input: 200-240 VAC, 1~, 24A, 50/60Hz

Output: 200-240 VAC, 1~, 24A MAX

C19: 16A PER OUTLET

PSE

Input: 200-240 VAC, 1~, 30A, 50/60Hz

Output: 200-240 VAC, 1~, 30A MAX

C19: 20A PER OUTLET

UL-EU

Input: 200-240 VAC, 1~, 24A, 50/60Hz

Output: 200-240 VAC, 1~, 30A MAX

C19: 16A PER OUTLET

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP6032A

Input: 200-240 VAC, 50/60Hz, 32A

Output: 200-240 VAC, 32A MAX

C19: 16A PER OUTLET 16A MAX PER BANK

AP6038A

Input: 200-240 VAC, 1~, 50/60Hz, 48A

Output: 200-240 VAC, 48A MAX

C19: 16A PER OUTLET

AP6120A

Input: 100-240 VAC, 1~, 16A, 50/60Hz

Output: 100-240 VAC

C13: 12A PER OUTLET

C19: 16A PER OUTLET

PSE

Input: 100-240 VAC, 1~, 20A, 50/60Hz

Output: 100-240 VAC

C13: 15A PER OUTLET

C19: 20A PER OUTLET

UL-EU

Input: 200-240 VAC, 1~, 16A, 50/60Hz

Output: 200-240 VAC

C13: 10A PER OUTLET

C19: 16A PER OUTLET

AP7541

Input: 200-240 VAC, 1~, 30A, 50/60Hz

Output: 200-240VAC, 24A

C19: 16A PER OUTLET

C13: 12A PER OUTLET

PSE

Input: 200-240 VAC, 1~, 30A, 50/60Hz

Output: 200-240 VAC, 30A

C19: 20A PER OUTLET

C13: 15A PER OUTLET

AP7567A

Input: 200-240 VAC, 3W+PE, 40A, 50/60Hz

Output: 200-240 VAC, 40A MAX

C19: 16A PER OUTLET

C13: 12A PER OUTLET

AP9559

Input: 100-240 VAC, 50/60Hz, 16A

Output: 100-240 VAC, 16A TOTAL

12A MAX PER C13 OUTLET (UL)

10A MAX PER C13 OUTLET (EU)

16A MAX PER C19 OUTLET (UL)

16A MAX PER C19 OUTLET (EU)

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP9562

Input: 100-120 VAC, 50/60Hz, 12A
Output: 100-240 VAC, 12A TOTAL
12A MAX PER OUTLET

PSE

Input: 100-120 VAC, 50/60Hz, 15A
Output: 100-120 VAC, 15A TOTAL
15A MAX PER OUTLET

AP9565

Input: 100-240 VAC, 50/60Hz, 16A
Output: 100-240 VAC, 16A TOTAL
12A MAX PER C13 OUTLET (UL)
10A MAX PER C13 OUTLET (EU)
12A MAX PER C13 OUTLET (KC)

AP9567

Input: 100-120 VAC, 50/60Hz, 12A
Output: 100-120 VAC, 12A TOTAL
12A MAX PER OUTLET

PSE

Input: 100-120 VAC, 50/60Hz, 15A
Output: 100-120 VAC, 15A TOTAL
15A MAX PER OUTLET

AP9568

Input: 100-240 VAC, 50/60Hz, 12A
Output: 100-240 VAC, 12A TOTAL (UL) 10A TOTAL (EU)
12A MAX PER C13 OUTLET (UL)
10A MAX PER C13 OUTLET (EU)

AP9570

Input: 200-240/208 VAC, 50/60Hz
Output: 208 VAC, 24A TOTAL
16A MAX PER BANK
16A MAX PER OUTLET

PSE

Input: 200 VAC, 50/60Hz, 30A
Output: 200 VAC, 30A TOTAL
16A MAX PER BANK
16A MAX PER OUTLET

AP9571A

Input: 200-240/208 VAC, 50/60Hz, 24A
Output: 208 VAC, 24A TOTAL
16A MAX PER BANK
12A MAX PER C13 OUTLET

PSE

Input: 200 VAC, 50/60Hz, 30A
Output: 200 VAC, 30A TOTAL
20A MAX PER BANK
15A MAX PER C13 OUTLET

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP9571AX459

Input: 200-208 VAC, 24A, 50/60Hz

Output: 208 VAC, 24A PER PHASE TOTAL

16A PER BANK MAX

C19: 16A PER OUTLET MAX

C13: 12A PER OUTLET 16A PER GROUP MAX

PSE

Input: 200 VAC, 30A, 50/60Hz

Output: 200 VAC, 30A PER PHASE TOTAL

20A PER BANK MAX

C19: 16A PER OUTLET MAX

C13: 10A PER OUTLET 10A PER GROUP MAX

AP9572

Input: 100-240 VAC, 50/60Hz, 16A

Output: 100-240 VAC, 16A TOTAL

12A MAX PER C13 OUTLET (UL)

10A MAX PER C13 OUTLET (EU)

12A MAX PER C13 OUTLET (KC)

Smart Models

AP7800B

Input: 100-120 VAC, 50/60Hz, 12A

Output: 100-120 VAC

12A MAX TOTAL

12A MAX PER OUTLET

PSE

Input: 100/120 VAC, 50/60Hz, 12A

Output: 100/120 VAC

12A MAX TOTAL

15A MAX PER OUTLET

AP7811B

Input: 200-240 / 208 VAC, 50/60Hz, 24A

Output: 200-240 / 208 VAC

24A MAX

16A MAX PER BANK

12A MAX PER IEC 320 C13 OUTLET

16A MAX PER IEC 320 C19 OUTLET

PSE

Input: 200 VAC, 50/60Hz, 30A

Output: 200 VAC

30A MAX

20A MAX PER BANK

15A MAX PER IEC 320 C13 OUTLET

20A MAX PER IEC 320 C19 OUTLET

AP7820B

Input: 100-240 VAC, 50/60Hz, 12A (UL) / 10A (EU)

Output: 100-240 VAC

12A MAX PER OUTLET (UL)

10A MAX PER OUTLET (EU)

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP7821B

Input: 100-240 VAC, 50/60Hz, 16A MAX

Output: 100-240 VAC

16A MAX TOTAL

12A MAX PER OUTLET (UL)

10A MAX PER OUTLET (EU)

AP7900B

Input: 100/120 VAC, 50/60Hz, 12A MAX (UL) 15A MAX (PSE)

Output: 100/120 VAC

12A MAX (UL)

15A MAX (PSE)

12A MAX PER OUTLET (UL)

15A MAX PER OUTLET (PSE)

AP7911B

Input: 200-240/208 VAC 50/60Hz, 24A

Output: 200-240/208 VAC, 24A TOTAL

16A MAX PER BANK

12A MAX PER IEC 320 C13 OUTLET

PSE

Input: 200 VAC, 50/60Hz, 30A

Output: 200 VAC, 30A TOTAL

20A MAX PER BANK

15 MAX PER IEC 320 C13 OUTLET

AP7920B

Input: 100-240 VAC, 50/60Hz, 12A

Output: 100-240VAC, 12A TOTAL

12A MAX PER OUTLET

UL-EU

Input: 220-240 VAC, 50/60Hz, 10A

Output: 220-240 VAC, 10A TOTAL

10A MAX PER OUTLET

AP7921B

Input: 100-240 VAC, 50/60Hz, 16A

Output: 100-240 VAC, 16A TOTAL

12A MAX PER OUTLET

UL-EU

Input: 220-240 VAC, 50/60Hz, 16A

Output: 220-240 VAC, 16A TOTAL

10A MAX PER OUTLET

Basic Models

AP7530J (PSE ONLY)

Input: 100-120 VAC, 20A, 50/60Hz

Output: 100-120 VAC, 20A MAX

5-15R: 15A PER OUTLET

AP7532J (PSE ONLY)

Input: 100-120 VAC, 30A, 50/60Hz

Output: 100-120 VAC, 30A MAX

5-15R: 15A PER OUTLET

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP7526 (EMEA ONLY)

Input: 220/380-240/415 VAC, 3W+N+PE, 32A, 50/60Hz

Output: 220-240 VAC, 32A MAX

C19: 16A PER OUTLET

AP7551 (EMEA ONLY)

Input: 200-240/208 VAC, 50/60Hz, 16A

Output: 200-240 / 208 VAC, 16A TOTAL

16A MAX PER BANK

10A MAX PER C13 OUTLET

16A MAX PER C19 OUTLET

AP7553 (EMEA ONLY)

Input: 200-240/208 VAC, 50/60Hz, 32A

Output: 200-240/208 VAC, 32A TOTAL

16A MAX PER BANK

10A MAX PER C13 OUTLET

16A MAX PER C19 OUTLET

AP7554 (EMEA ONLY)

Input: 200-240/208 VAC, 50/60Hz, 16A

Output: 200-240 /208 VAC, 16A TOTAL

16A MAX PER BANK

10A MAX PER C13 OUTLET

16A MAX PER C19 OUTLET

AP7555A (EMEA ONLY)

Input: 220/380-240/415 VAC, 3W+N+PE, 32A

Output: 220-240 VAC, 32A TOTAL

16A MAX PER OUTLET

AP7557 (EMEA ONLY)

Input: 220/380-240/415 VAC, 3W+N+PE, 16A

Output: 220-240 VAC, 16A TOTAL

16A MAX PER OUTLET

Smart Models:

AP7802BJ (PSE ONLY)

Input: 100-120 VAC, 50/60Hz, 30A

Output: 100-120 VAC, 30A TOTAL

15A MAX PER OUTLET

20A MAX PER BANK

AP7902BJ (PSE ONLY)

Input: 100-120 VAC, 50/60Hz, 30A

Output: 100-120 VAC, 30A TOTAL

15A MAX PER OUTLET

20A MAX PER BANK

AP7822B (EMEA ONLY)

Input: 220-240 VAC, 50/60Hz, 32A

Output: 220-240 VAC, 32A TOTAL

16A MAX PER BANK

10A MAX PER C13 OUTLET

16A MAX PER C19 OUTLET

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36671-M1-UL

Ratings:

AP7850B (EMEA ONLY)

Input: 220-240 VAC, 50/60Hz, 10A

Output: 220-240 VAC, 10A TOTAL

10A MAX PER C13 OUTLET

AP7922B (EMEA ONLY)

Input: 220-240 VAC, 50/60Hz, 32A

Output: 220-240VAC, 32A TOTAL

16A MAX PER BANK

10A MAX PER C13 OUTLET

AP7950B (EMEA ONLY)

Input: 200-240/208 VAC, 50/60Hz, 10A

Output: 200-240/208 VAC, 10A TOTAL

10A MAX PER BANK

10A MAX PER C13 OUTLET

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

- Model AP6007A was submitted for a heating and an electrical strength test to increase the Tma from 25C to 60C.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-10-15

Original Issue Date: 2020-09-24

Signature:

Jolanta M. Wroblewska