

CERTIFICATE

Issued to:

Applicant:

American Power Conversion Holdings Inc., Taiwan
Branch
5F., No. 189, Sec. 2, Jiuzong Rd., Neihs Dist.,
11494 Taipei City, Taiwan

Licensee:

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie
Town,
523963 Dongguan, Guangdong, China

Product : Plug-in adaptors with Surge Protective Device
Trade name(s) : APC or APC by Schneider Electric
Type(s)/model(s) : PM1WU2-GR and PM1WU2-RS

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, IEC 60884-2-5:2017, NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019, NEN-IEC 60884-1:2019/A2:2019, DIN VDE 0620-2-1:2016, DIN VDE 0620-2-1:2016/A1:2017, EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020, EN 61643-11:2012 and EN 61643-11:2012/A11:2018
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2025917


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 11 January 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 35-113911 REV.1

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



K. Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Plug-in adaptors with Surge Protective Device
Trade name(s)	: APC or APC by Schneider Electric
Type(s)/model(s)	: PM1WU2-GR and PM1WU2-RS
Ratings	: 16 A MAX. / MAX. 3680 W, 250 V~ USB Output: 5,0 V dc 2,4 A (Shared) 12,0 W
Earthing	: with earthing-contacts
Standard sheet	: plug portion: Standard sheet VII of NEN 1020 socket portion: Standard sheet III of NEN 1020
Description	: housing of thermoplastic material, with shutter provided with AC Surge Protective Device and dual output USB-Charger

TESTS**Test requirements**

IEC 60884-1:2002
IEC 60884-1:2002/A1:2006
IEC 60884-1:2002/A2:2013
IEC 60884-2-5:2017
NEN 1020:2019
NEN-IEC 60884-1:2019
NEN-IEC 60884-1:2019/A1:2019
NEN-IEC 60884-1:2019/A2:2019
DIN VDE 0620-2-1:2016
DIN VDE 0620-2-1:2016/A1:2017
EN IEC 62368-1:2020
EN IEC 62368-1:2020/A11:2020
EN 61643-11:2012
EN 61643-11:2012/A11:2018

Test result

The test results are laid down in DEKRA test file 610689500, 437680500, 437680600.

Additional information

The product also complies with Clause 10.5 of DIN VDE 0620-2-1:2021.

This certificate replaces certificate No. 35-113911 which we hereby declare invalid.

The list of components is laid down in test report 4376805.50,4376806.50,6106895.50.

Conclusion

The examination proved that all requirements were met.

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie Town,
523963 Dongguan, Guangdong, China