

Basic Rack PDU


Overview

The American Power Conversion (APC[®]) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has thirty-six (36) IEC-309-C13 outlets and six (6) IEC-309-C19 outlets.

Power cord. The 3-ft (0.91-m) power cord terminates with an IEC-309 20-A plug.

AP7557NA



Specifications

Electrical

Input connection	IEC-309, 20 A
Input power	11.0 kVA
Acceptable input voltage	220–240/380–415 VAC
Maximum input current (phase)	20 A
Derated input current (phase)	16 A
Input frequency	50/60 Hz
Output voltage	240 VAC (line to neutral)
Output connections	(36) IEC-309-C13 (6) IEC-309-C19
Cord length	3.00 ft (0.91 m)
Maximum output current (outlet)	10 A–IEC-309-C13 16 A–IEC-309-C19
Maximum output current (phase)	16 A

Physical

Dimensions (H x W x D)	70.00 x 2.19 x 1.73 in (177.80 x 5.56 x 4.39 cm)
Shipping dimensions (H x W x D)	84.00 x 6.00 x 5.00 in (213.36 x 15.24 x 12.7 cm)
Weight	12.37 lb (5.61 kg)
Shipping weight	20.68 lb (9.38 kg)

Environmental

Maximum elevation (above MSL)	
Operating	10,000 ft (3000 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	23 to 115°F (–5 to 45°C)
Storage	–13 to 149°F (–25 to 65°C)
Humidity	
Operating	5–95% RH, non-condensing
Storage	5–95% RH, non-condensing

Compliance

Safety verification	UL/cUL: UL60950-1
---------------------	-------------------

Customer support and warranty information is available at the APC Web site, www.apc.com.

© 2008 American Power Conversion. All rights reserved. All APC trademarks are property of American Power Conversion. Other trademarks are property of their respective owners.



990-3371
06/2008

