

- NOTES:**
- 1.INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
 - 2.REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
 - 3.ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
 - 4.WEIGHT OF THE UNIT IS 109kg [240.3 lb].
 - 5.FRONT AND REAR CLEARANCE ARE FOR AIRFLOW AND SERVICE ACCESS, TOP AND RIGHT SIDE CLEARANCE ARE FOR SERVICE ACCESS ONLY.
CONSULT WITH THE LOCAL SAFETY CODES AND STANDARDS FOR ANY ADDITIONAL REQUIREMENTS OF LOCAL AREA.
IF THE UPS IS INSTALLED WITHOUT SIDE ACCESS, THE LENGTH OF CABLES CONNECTED TO THE UPS MUST ALLOW FOR ROLLING OUT THE UPS.
 - 6.COLOR: RAL 9003.
 - 7.PROTECTION CLASS: IP20.
 - 8.OPERATING TEMPERATURE: 0°C TO 40°C [32°F TO 104°F].

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.


Schneider Electric

TITLE:
Schneider Electric Easy UPS 3M
60kVA, 400V, 3PH
WITHOUT BATTERY MODULES
GENERAL ARRANGEMENT

PROJECT: SUBMITTAL DRAWINGS SHEET 1 OF 6

DWG NO: E3MUPS60KH
DRAWN: DIBYA/JAYAPRAKASH
ENGINEER: Compbell BAI
APPROVED: YoPing YANG

REV. 1
FIRST
ANGLE
PROJECTION



NOTES:

- 1.INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
- 2.REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
- 3.ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

Schneider Electric

TITLE:
Schneider Electric Easy UPS 3M
60kVA, 400V, 3PH
WITHOUT BATTERY MODULES
TOP & BOTTOM VIEW

PROJECT: SUBMITTAL DRAWINGS SHEET 2 OF 6

DWG NO:	E3MUPS60KH	REV:	1
DRAWN:	DIBYA/JAYAPRAKASH	11-JUN-24	FIRST
ENGINEER:	Compbell BAI	11-JUN-24	ANGLE
APPROVED:	YaPing YANG	11-JUN-24	PROJECTION



- NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
 2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
 3. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

Schneider Electric


TITLE:
Schneider Electric Easy UPS 3M
60kVA, 400V, 3PH
WITHOUT BATTERY MODULES
INTERNAL FRONT AND REAR VIEW

PROJECT: SUBMITTAL DRAWINGS SHEET 3 OF 6


DWG NO: E3MUPS60KH

DRAWN: DIBYA/JAYAPRAKASH	11-JUN-24
ENGINEER: Compbell BAI	11-JUN-24
APPROVED: YoPing YANG	11-JUN-24


REV. 2
FIRST ANGLE PROJECTION



DETAIL-B, ENLARGED
CONNECTION TERMINALS



VIEW-C (ENLARGED)
INPUT CONTACTS AND OUTPUT RELAYS



PARALLEL CONNECTION

- NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
 2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.
 3. UP TO 6 NUMBERS OF UPS CAN BE CONNECTED IN PARALLEL.
MAXIMUM PARALLEL COMMUNICATION CABLE LENGTH IS 5.0METERS.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

Schneider Electric

TITLE:
Schneider Electric Easy UPS 3M
60KVA, 400V, 3PH
WITHOUT BATTERY MODULES
ENLARGED VIEWS AND DETAILS

PROJECT: SUBMITTAL DRAWINGS SHEET 4 OF 6


DWG NO: E3MUPS60KH

DRAWN:	JAYAPRAKASH	24-JAN-19
ENGINEER:	Compbell BAI	30-JAN-19
APPROVED:	YoPing YANG	30-JAN-19


REV.

FIRST	ANGLE
PROJECTION	

SINGLE MAINS CONFIGURATION



DUAL MAINS CONFIGURATION



NOTES:

- 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
- 2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK
- 3. DRAWING DEPICTS POWER SYSTEM CONNECTIONS AND IT IS NOT REPRESENTATIVE OF PHYSICAL LAYOUT.
- △ SINGLE MAINS CONFIGURATION IS DEFAULT.
FOR DUAL MAINS CONFIGURATION REMOVE THE 3 SHORTING COPPER BARS.
- △ BATTERIES CAN BE CONNECTED IN SERIES DEPENDING UPON THE RUNTIME REQUIREMENTS.
- 6. UP TO 6 UPS CAN BE CONNECTED IN PARALLEL.
- △ REFER TO SHEET-6 FOR ELECTRICAL DATA.
- △ 1xPOWER MODULES RATED AT 60KVA.
- 9. CABLE LUGS ARE PROVIDED BY OTHERS.

LEGEND:
----- CABLE PROVIDED BY OTHERS

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE:
Schneider Electric Easy UPS 3M
60KVA, 400V, 3PH
WITHOUT BATTERY MODULES
SYSTEM ON-LINE DIAGRAM
PROJECT: SUBMITTAL DRAWINGS SHEET 5 OF 6

DWG NO: E3MUPS60KH
DRAWN: JAYAPRAKASH 09-NOV-21
ENGINEER: Compbell BAI 09-NOV-21
APPROVED: YoPing YANG 09-NOV-21

REV. 1
FIRST ANGLE PROJECTION

ELECTRICAL DATA SHEET	
UPS RATING	60kVA
INPUT SPECIFICATIONS	
INPUT WIRING	3W+N+PE
INPUT VOLTAGE (V)	380/400/415
NOMINAL INPUT CURRENT (A)	96/91/88
MAXIMUM INPUT CURRENT (A)	109/104/100
INPUT CURRENT LIMITATION (A)	155
INPUT FREQUENCY (Hz)	40 - 70
INPUT POWER FACTOR	>0.99
MAXIMUM INPUT SHORTCIRCUIT WITHSTAND (kA)	Icw= 10
PROTECTION	FUSE
RAMP-IN (SECONDS)	7
INPUT THDI - LINEAR LOAD	< 3%
BYPASS SPECIFICATIONS	
BYPASS WIRING	3W+N+PE
OVERLOAD CAPACITY	110% FOR 60 MINUTES
	130% FOR 10 MINUTES
	130-150% FOR 1 MINUTE
	>150% FOR 1200 MILLISECONDS
BYPASS VOLTAGE (V)	380/400/415
MINIMUM BYPASS VOLTAGE (V)	266/280/291
MAXIMUM BYPASS VOLTAGE (V)	475/480/477
NOMINAL BYPASS CURRENT (A)	91/87/83
BYPASS FREQUENCY (Hz)	50/60
MAXIMUM INPUT SHORTCIRCUIT WITHSTAND (kA)	Icw= 10
OUTPUT SPECIFICATIONS	
OUTPUT WIRING	3W+N+PE
OVERLOAD CAPACITY AT 30°C	110% FOR 60 MINUTES
	125% FOR 10 MINUTES
	150% FOR 1 MINUTE
	>150% FOR 1200 MILLISECONDS
OUTPUT VOLTAGE (V)	380/400/415 (±1%)
NOMINAL OUTPUT CURRENT (A)	91/87/83
OUTPUT FREQUENCY (Hz)	50/60
OUTPUT POWER FACTOR	1
OUTPUT THDU	<3% @ 100% LINEAR LOAD, < 5% @ 100% NON-LINEAR LOAD
BATTERY SPECIFICATIONS	
CHARGING POWER IN % OF OUTPUT POWER	1-20%
MAXIMUM CHARGING POWER (W)	12000
NOMINAL BATTERY VOLTAGE (32-50 Blocks) (VDC)	±192 to ±300
NOMINAL FLOAT VOLTAGE (32-50 Blocks) (VDC)	±215.5 to ±337.5
END OF DISCHARGE VOLTAGE (32-50 Blocks) (VDC)	±153.6 to ±240
BATTERY CURRENT AT FULL LOAD AND NOMINAL BATTERY VOLTAGE (36-50 Blocks) (A)	147-105
BATTERY CURRENT AT FULL LOAD AND MINIMUM BATTERY VOLTAGE (36-50 Blocks) (A)	185-132
TEMPERATURE COMPENSATION (PER CELL) IF THE TEMPERATURE IS ABOVE 28°C	PROGRAMMABLE FROM 0-7mV. DEFAULT IS 3mV
RIPPLE CURRENT	<5% C10

RECOMMENDED CABLE SIZES			
	CABLE SIZE PER PHASE (mm²)	NEUTRAL CABLE SIZE (mm²)	PE CABLE SIZE (mm²)
INPUT	35	2x25	16
BYPASS	25		16
OUTPUT	25	2x25	16
BATTERY	50	-	25

NOTES:

1.INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL REGULATIONS.

2.REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND SITE PREPARATION WORK.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: Schneider Electric Easy UPS 3M 60kVA, 400V, 3PH WITHOUT BATTERY MODULES ELECTRICAL DATA	
PROJECT: SUBMITTAL DRAWINGS	SHEET 6 OF 6

DWG NO: E3MUPS60KH		REV. 1
DRAWN: JAYAPRAKASH	29-MAR-19	FIRST ANGLE PROJECTION
ENGINEER: Compbell BAI	29-MAR-19	
APPROVED: YaPing YANG	29-MAR-19	