

CERTIFICATE

Issued to:

Applicant:

American Power Conversion Holdings Inc., Taiwan
Branch
5F., No. 189, Sec. 2, Jiuzong Rd., Neihu Dist.,
11494 Taipei City, Taiwan

Licensee:

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie
Town,
523963 Dongguan, Guangdong, China

Product : Multiple portable socket-outlets with SPD(s)
Trade name(s) : APC or APC by Schneider Electric
Type(s)/model(s) : PM5-FR, PM5T-FR and PM5V-FR

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, IEC 60884-2-7:2011, IEC 60884-2-7:2011/A1:2013, NF C 61-314:2017, EN 61643-11:2012, EN 61643-11:2012/A11:2018, EN 61643-21:2001, EN 61643-21:2001/A1:2009 and EN 61643-21:2001/A2:2013
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2025917


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 20 January 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 35-121967

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



M. Triulzi
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Multiple portable socket-outlets with SPD(s)
Trade name(s)	: APC or APC by Schneider Electric
Type(s)/model(s)	: PM5-FR, PM5T-FR and PM5V-FR
Rated current	: 16 A
Rated voltage	: 250 V~
Rated power	: (MAX. 2300 W, 230 V~, 10 A, limited by means of circuit breaker)
Earthing	: with earthing-pin
Design	: non-rewirable, with shutters
Standard sheet	: I of NF C61-314
Applied flexible cord	: H05VV-F 3G1,0 mm ²
Certification mark	: complies with the requirements
Cord termination	: soldered connection
Description	: body of thermoplastic material

Product data – type PM5-FR

Design	: 5-fold, provided with circuit-breaker, two-pole rocker switch and AC Surge Protective Device
--------	--

Product data – type PM5T-FR

Design	: 5-fold, provided with circuit-breaker, two-pole rocker switch, AC Surge Protective Device and Phone Surge Protective Device
--------	---

Product data – type PM5V-FR

Design	: 5-fold, provided with circuit-breaker, two-pole rocker switch, AC Surge Protective Device and TV Surge Protective Device
--------	--

TESTS**Test requirements**

IEC 60884-1:2002
IEC 60884-1:2002/A1:2006
IEC 60884-1:2002/A2:2013
IEC 60884-2-7:2011
IEC 60884-2-7:2011/A1:2013
NF C 61-314:2017
EN 61643-11:2012
EN 61643-11:2012/A11:2018
EN 61643-21:2001
EN 61643-21:2001/A1:2009
EN 61643-21:2001/A2:2013

Test result

The test results are laid down in DEKRA test file 611076400, 437729100.

Additional information

The list of components is laid down in test report 4377291.50/51+6110764.50/51/52.

Conclusion

The examination proved that all requirements were met.

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie Town,
523963 Dongguan, Guangdong, China