

Date : 15.07.2020

American Power Conversion Holding
Inc., Taiwan Branch
5F., No. 189, Sec. 2, Jiuzong Rd.,
Taipei City 11494
Taiwan, R.O.C.
Attn: Ken Hsieh

Re. : CU US + Canada Certificate

Type of Equipment : APC Charge Mobile Power Supply for Surface Hub 2
Model Designation : See Certificate
Certificate No. : CU 72202540 0001
File No. : 50383376 001
Engineer/Contact : Andreas Klinker
Standard(s) : UL 62368-1:2014
CAN/CSA-C22.2 NO. 62368-1-14

Dear Madame or Sir,

The above referenced technical equipment has been tested and was found to be in compliance with the listed test requirement(s). Enclosed, please find the TUV Rheinland approval document No. CU 72202540 0001. It authorizes you to label the listed product(s) with the TUV Rheinland Mark identified in the approval document. For compliance, the Test Mark must be on the approved unit.

Your product is subject to regular factory follow-up inspections as well as annual certificate and factory registration fees.

In using the TUV Rheinland Mark you are obligated to comply with the TUV Rheinland of North America Service Agreement.

If we can be of any further assistance to you, please do not hesitate to contact us.

Sincerely yours,
Certification Body

H. Lin 
QA Certification Officer

Enclosure

Certificate



Certificate no.

CU 72202540 01

License Holder:

American Power Conversion Holding
Inc., Taiwan Branch
5F., No. 189, Sec. 2, Jiuzong Rd.,
Taipei City 11494
Taiwan

Manufacturing Plant:

ZHONGSHAN VOLTRONIC POWER
ELECTRONICS LIMITED
No. 8 Shichong Road,
Zhongshan Torch Hi-Tech
Industrial Development Zone,
Zhongshan, Guangdong,
P.R. China

Test report no.: USA-AK 50383376 001

Client Reference:

Tested to: UL 62368-1:2014
CAN/CSA-C22.2 NO. 62368-1-14

Certified Product: APC Charge Mobile Power Supply for Surface Hub 2 License Fee - Units


Model Designation: CSH2, CSH2-I (APC)
Rated Voltage : AC 110-240V, 50-60Hz
Rated Current : 8A max.
Output ratings : 1) AC 110-240V, 50-60Hz, 4A max., 403W max.
2) DC 24V, 16.2A max., 388W max.
Protection Class: I
Rated Ambient Temperature : +40°C max.

7

7

Appendix: 1, 1-17

Licensed Test mark:



Date of Issue
(day/mo/yr)
14/07/2020