

## SRVPM1KRIL

APC Easy UPS On-Line, 1000VA/800W,  
Rackmount 2U, 230V, 4x IEC C13 outlets,  
Intelligent Card Slot, LCD, Extended runtime,  
No Battery, W/O rail kit



EAN Code: 0731304402954



### Commercial status

End of Commercialisation :

⚠ End of Commercialisation

### Overview

Presentation High quality, Double-conversion On-line UPS designed for essential power protection needs ev

### Main

Main Input Voltage	230 V AC 1 phase
Input voltage	220 V 240 V
Input Connection Type	IEC 60320 C14
Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing
Output voltage	230 V AC 1 phase
Output voltage	220 V 240 V
Rated power in W	800 W
Rated power in VA	1000 VA
Output connection type	4 IEC 60320 C13
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1
Harmonic distortion	3 %
Maximum configurable power in VA	1000 VA
Maximum configurable power in W	800 W
UPS type	On-Line
Wave type	Sine wave
Efficiency	88 % (full load)
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Complementary

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery type	Lead-acid external sold separately
Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
UPS connectivity	Serial port USB port Available expansion slot
Surge energy rate	600 J
Number of rack unit	2U
Cable length	1.5 M
Number of cables	1
Colour	Black (RAL 7010)
Height	86 Mm
Width	438 Mm
Depth	332 Mm
Product weight	6 Kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
USB compatible	Yes
Mounting position	Horizontal
Mounting mode	Rack-mounted with kit sold separately
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of product	Easy UPS On-Line
Product or component type	Uninterruptible power supply (UPS)

## Environment

Product certifications	CE[RETURN]UKCA[RETURN]EAC[RETURN]TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...50 °C
Storage altitude	0...15000 M
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	50 dBA
Heat dissipation	372 Btu/H
Operating altitude	0...3000 m

## Batteries & Runtime

Battery type	External battery system
Battery voltage	36 V
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery charger power	175 W rated

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 Cm
Package 1 Width	44.5 Cm
Package 1 Length	55.0 Cm
Package 1 Weight	9.3 Kg

## Offer Sustainability

Recyclability potential, in %	65
Total lifecycle Carbon footprint	1 838 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	73.18905383652299
Carbon footprint of the manufacturing phase [A1 to A3]	73 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.8100697549633339
Carbon footprint of the distribution phase [A4]	0.8 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	9539.7295431472
Carbon footprint of the use phase [B2, B3, B4, B6]	9 540 kg CO2 eq.
Mercury free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	0.7135932749060991
Carbon footprint of the end-of-life phase [C1 to C4]	0.7 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Total lifecycle Carbon footprint	1838
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	080b8d64-796e-42e7-a17d-31b86e55d143
REACH Regulation	Reference contains Substances of Very High Concern above the threshold <a href="#">↗</a>
EU RoHS Directive	Compliant By Exemption <a href="#">↗</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection a

## Logistical informations

Country of origin	CN
-------------------	----

## Contractual warranty

Warranty (in months)	24
----------------------	----

Product Life Status : **End of commerc. - Block**

SRVPM1KRIL may be replaced by any of the following products:



### SRV2KRILRK-E

APC Easy UPS On-Line, 2000VA/1800W, Rackmount 4U, 230V, 4x IEC C13 outlets, Intelligent Card Slot, LCD, Extender

Qty 1

Substitution date: |



### SRVPM1KRIL-E

APC Easy UPS On-Line, 1000VA/900W, Rackmount 2U, 230V, 4x IEC C13 outlets, Intelligent Card Slot, LCD, Extender

Qty 1

Substitution date: |