



NEMA TYPE 1
NO KNOCKOUTS

NOTES:
FINISH - GRAY BAKED ENAMEL
CSA CERTIFIED - FILE # LL-89067
ALL NEUTRALS - INSULATED GROUNDABLE
FUSIBLE SWITCHES ARE SUITABLE FOR USE AS SERVICE EQUIPMENT.
SHORT CIRCUIT CURRENT RATINGS:
10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES
200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R FUSES HAVING
CLASS R REJECTION KITS INSTALLED OR CLASS J FUSES.



TERMINAL LUGS DATA			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
400	(1) 750 KCMIL OR	(1) #1/0 AWG OR	AL OR CU
	(2) 300 KCMIL	(2) #1/0 AWG	

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG.	HORSEPOWER RATINGS						
			240VAC		480VAC		600VAC		250 VDC
			MAX.	STD.	MAX.	STD.	MAX.	STD.	
CH365	600VAC;250VDC	A	-	100	250	125	350	50	
CH365N	600VAC	B	-	100	250	125	350	-	
CHU365	600VAC;250VDC	C	125	-	250	-	350	50	

HEAVY DUTY SAFETY SWITCHES
VISIBLE BLADE TYPE
400 AMPERE
ENCLOSURE - NEMA TYPE 1 GENERAL PURPOSE



DWG# 1922C
NO.

REF DWG #1922