



## UK DECLARATION OF CONFORMITY

**We : MANUFACTURER**  
**Schneider Electric Industries SAS**  
**35 rue Joseph Monier**  
**Rueil Malmaison 92500 – France**

**UK REPRESENTATIVE**  
**Schneider Electric Limited**  
**Stafford Park 5**  
**Telford, TF3 3BL - United Kingdom**

Hereby declare under our sole responsibility that the products:

Trademark	Schneider Electric
Product, Type	METSECT5XXYYY Current Transformers
List of reference and options	See next pages

Are in conformity with the requirements of the following regulations, which was demonstrated by application the following designated standards.

Regulation	Designated standard / Notified body reference
<b>Electrical Equipment (Safety) Regulations</b> SI 2016 No. 1101	BS EN 61869-1:2009 BS EN 61869-2:2012
<b>The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012</b> SI 2012 No. 3032	BS EN IEC 63000:2018

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions and to accepted rules of the art.

This declaration becomes invalid in the case of any modification to the products not authorized by us.

**Person in charge of the documentation (Manufacturer):**


Kumudha V  
 Schneider Electric Pvt. Ltd.  
 12A, Attibele Industrial Area,  
 Neralur (PO), Bangalore -562107 - India

**Issued at Telford - United Kingdom (Importer): date & Signature:** 28-6-2022

DocuSigned by:  
  
 485DFE6A98894C3...  
**Name : David WILLIAMS**  
 VP Marketing UK&I  
 Zone UK & Ireland



## UK DECLARATION OF CONFORMITY

	<p>Schneider Electric split core CTs have a 5A secondary current rating and support for primary currents ranging from 100A to 4000A.</p>
---	--

## Annex : Applied BS standards

Series	Commercial reference(s)	UKCA marking initial application date	Applicable standards
Split Core Current Transformers	METSECT5[xx][yyy]	2022	<p><b>As Current transformers:</b></p> <ul style="list-style-type: none"> <li>■ BS EN 61869-1:2009</li> <li>■ BS EN 61869-2:2012</li> <li>■ BS EN 63000:2018</li> </ul>

**Where:**

[xx] stands for the form factor - GA, GD, GG, GJ, HA, HD HJ, HG, HM, HP

[yyy] stands for the nominal primary current in Amperes - 010, 015, 020, 025, 030, 040, 050, 060, 075, 080, 100, 120, 125, 150, 160, 200, 250, 300 and 400