


NEMA TYPE 3R



TERMINAL LUGS ‡

AMPERES	MAX WIRE	MIN WIRE	TYPE
200	250 KCMIL	#6 AWG	AL OR CU

KNOCKOUTS

SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	45
E	1.50	38	2.00	51
F	2.00	51	2.50	64
G	2.50	64	3.00	76
H	3.00	76	3.50	89

DUAL DIMENSIONS: INCHES  
MILLIMETERS

NOTES:  
 FINISH - GRAY BAKED ENAMEL  
 cUL LISTED - FILE E-2875  
 ALL NEUTRALS - INSULATED GROUNDABLE  
 FUSIBLE SWITCHES ARE SUITABLE FOR USE AS SERVICE EQUIPMENT  
 SHORT CIRCUIT CURRENT RATINGS:  
 10,000 AMPERES WITH CLASS H OR K FUSES.  
 200,000 AMPERES WITH CLASS R FUSES HAVING CLASS R REJECTION KITS INSTALLED  
 OR CLASS J FUSES.  
 ON 600V SWITCHES, 100,000 AMPERE MAX ON CORNER GROUNDED DELTA WHEN  
 PROTECTED BY CLASS R OR J FUSES.  
 WHEN MOUNTING THESE SWITCHES, ALLOW 4.00/[102] MIN CLEARANCE BETWEEN  
 ENCLOSURES FOR OPENING OF SIDE HINGED DOOR.  
 ▲TYPE 3R SWITCHES HAVE PROVISIONS FOR MAXIMUM 2.50/[64] BOLT-ON HUB.  
 ‡LUGS SUITABLE FOR 75°C CONDUCTORS.  
 #IF CORNER GROUNDED DELTA, USE OUTER SWITCHING POLES FOR UNGROUNDED CONDUCTORS.  
 &IF CORNER GROUNDED DELTA, INSTALLED NEUTRAL AND USE OUTER SWITCHING POLES FOR UNGROUNDED CONDUCTORS.  
 ~ USE ANY TWO SWITCHING POLES.  
 < MAX RATING.

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG	HORSEPOWER RATINGS										250 VDC STD	600 VDC STD		
			240VAC		480VAC		600VAC		250 VDC	600 VDC						
			STD	MAX	STD	MAX	STD	MAX								
CH224NRB	240VAC;250VDC	B	15	25#	-	60#	-	-	-	-	-	-	-	40	-	
CH324NRB	240VAC;250VDC	A	15^	25#	-	60#	-	-	-	-	-	-	-	40	-	
CH364RB	600VAC;600VDC	C	15^	25#	-	60&	25^	50&	50^	125&	30^	60	50^	150	40^	50^
CH364NRB	600VAC;600VDC	A	15^	25&	-	60#	25^	50#	50^	125#	30^	60	50^	150	40^	50^
CHU364RB	600VAC;600VDC	D	-	-	15^	60&	-	-	50^	125&	-	-	50^	150	40^ <	50^ <

HEAVY DUTY SAFETY SWITCHES  
 VISIBLE BLADE TYPE  
 200 AMPERE - SERIES F5  
 ENCLOSURE - NEMA TYPE 3R RAINPROOF

**SQUARE D COMPANY**

DWG# 3262C  
NO.