


MULTIPLES OF RATED CURRENT



HD, HG, HJ, HL MOLDED CASE CIRCUIT BREAKERS
CHARACTERISTIC TRIP CURVE NO. 50-2

CIRCUIT BREAKER INFORMATION

Circuit Breaker Prefix	Continuous Ampere Rating	Maximum AC Voltage	Number of Poles
HD, HG, HJ, HL	40-60	600	2, 3

This curve is to be used for application and coordination purposes only. The **EZ-AMP** overlay feature at the bottom of the page should be used during coordination studies.

All time/current characteristic curve data is based on 40°C ambient cold start. Terminations are made with conductors of appropriate length and ratings.

MAXIMUM SINGLE-POLE TRIP TIMES
AT 25°C BASED ON NEMA AB-4 2003

MAXIMUM CLEARING TIME
(AT 50 Hz) (AT 60 Hz)


1 CYCLE
(60 Hz)

1 CYCLE
(50 Hz)

1/2 CYCLE
(60 Hz)

1/2 CYCLE
(50 Hz)

MULTIPLES OF RATED CURRENT



EZ-AMP™