

70-750E8-1

Socket, SE Relays general purpose relay accessory, DPDT, 12A, 300 V, 8 pins, lift terminals, 750/750H series

Product availability: Stock - Normally stocked in distribution facility



Commercial status

This Product is Obsolete : OCT 22, 2024

⚠ This Product is Obsolete

Main

Range of Product	Legacy
Product or Component Type	Socket
Product compatibility	relay 750XCXR[RETURN] relay 750XBXH[RETURN] diode 70-ASMD[RETURN] suppressor module 70-ASMM[RETURN] signalling device 70-ASMLG[RETURN] suppressor module 70-ASMR[RETURN] jumper wire 16-750CBJ-1
Number of terminals	8
Switch Function	DPDT
Contacts type and composition	2 NO + 2 NC

Complementary

Line Rated Current	12 A
[Ue] rated operational voltage	300 V
Contact terminal arrangement	Separate
Connections - terminals	Lift terminals flexible lift terminals solid
Tightening torque	< 0.8 N.m
Fixing mode	By screw M3.5, M3.5 panel Clip-on 35 mm DIN rail
Shape of screw head	Combination roundhead
Net Weight	3.0 Oz (85 g)
Width	1.5 In (38 mm)
Depth	2.2 In (57 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480278020
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.24 In (5.7 cm)
Package 1 Width	1.50 In (3.8 cm)
Package 1 Length	2.24 In (5.7 cm)
Package 1 Weight	3.0 Oz (85 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1

Product Life Status : **End of commercialisation**