



NMTR.E164867 Power Circuit and Motor-mounted Apparatus

[Page Bottom](#)

Power Circuit and Motor-mounted Apparatus

[See General Information for Power Circuit and Motor-mounted Apparatus](#)

TELEMECANIQUE
PO BOX 27446
RALEIGH, NC 27611 USA

E164867

Busbar systems, Series AK5:

Busbar, Model AK5, followed by JB, followed by -133, -134, -135, -143, -144, -145, -146, -149, -1410; **Plate**, Model AK5, followed by PA211 N1, -211 N2, -211 N3, -211 Ph3, -211 Ph12, -211 Ph23, -231, -232, -232S, -241, -242, -532, -542, -2311, -2312, -2312S, -5312, PE17, -27; **Plug**, Model AK5, followed by PC, followed by -12, -12PH, -13, -14, -32L, -32LPH, -33, -33L, -34, -34L, -131, -331.

Buzzer element, Cat. No. XVPC, followed by 09, may be followed by B, G or M, may be followed by W.

Mounting rod, Cat. No. XVPC, followed by 02, 03 or 04, may be followed by W.

Open type linear power supplies, Models ABL8 FEQ24005, ABL8 FEQ24010, ABL8 FEQ24020, ABL8 FEQ24040, ABL8 FEQ24060, ABL8 FEQ24100, ABL8 FEQ24150, ABL8 FEQ24200, ABL8 TEQ24100, ABL8 TEQ24200, ABL8 TEQ24300, ABL8 TEQ24400, ABL8 TEQ24600.

Power supplies, Cat. No. ABL7, followed by RE or RP, followed by 12, 24 or 48, followed by 02, 03, 05 or 10.

Cat. No. ABL1, followed by REM, RPM, followed by 12050, 12083, 24025, 24042, 24062, 24100.

Cat. No. ASI, followed by ABL, followed by B, D or M, followed by 300 or 302, may be followed by 2 or 4.

Cat. Nos. ABL8MEM05040, ABL8MEM12020, ABL8MEM24012, ABL8MEM24003, ABL8MEM24006, ABL8REM24030.

Cat. Nos. ABL8 BUF 24400, ABL8 RED 24400, ABL8 DCC 12020, ABL8 DCC 05060.

Power supplies for use in industrial control equipment, Models ABL7CEM24003, -24006, -24012.

Signal lights, Cat. Nos. XVPC, followed by 33, 34, 35, 36, 37, 38, 6B3, 6B4, 6B5, 6B6, 6B7, 6B8, 6G3, 6G4, 6G5, 6G6, 6G7, 6G8, 6M3, 6M4, 6M5, 6M6, 6M7 or 6M8, may be followed by W.

Wiring base, Cat. No. XVPC, followed by 21, may be followed by W or WR.

[Last Updated on 2007-03-30](#)

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2007 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner,

without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2007 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

