



Basic Rack PDU


Overview

The APC Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has four (4) IEC-320-C19 outlets.

Power cord. The 12-foot (3.65-meter) power cord terminates with a NEMA L6-30 connector.

AP9570



Schneider
Electric

Specifications

Electrical

Input connector	NEMA L6-30 connector
Output connectors	4 – IEC 320-C19 outlets
Nominal input voltage	200–240 VAC
Acceptable input voltage	± 10% of normal voltage
Input frequency	50/60 Hz
Maximum total current draw	30A (PSE) 24A (cULus)
Overcurrent protection (internal)	(2) 20 A, 2-pole breakers

Physical

Size (H × W × D)	1.75 × 17.60 × 2.78 in (4.45 × 44.70 × 7.06 cm)
Shipping Dimensions (H × W × D)	6.75 × 19.00 × 6.875 in (17.14 × 48.26 × 17.46 cm)
Weight	6.0 lb (2.72 kg)
Shipping weight	8.5 lb (3.86 kg)

Environmental

Elevation (above MSL)	
Operating	0–10,000 ft (0–3000 m)
Storage	0–50,000 ft (0–15 000 m)
Temperature	
Operating	0–45° C (32–115° F)
Storage	–25–65° C (–13–149° F)
Humidity	
Operating	0–95% RH, Non-condensing
Storage	0–95% RH, Non-condensing

Compliance

Safety verification	cULus, PSE
---------------------	------------

Customer support and warranty information is available at www.apc.com.

© 2021 Schneider Electric. All rights reserved.