

Programmable Controllers

COMPANY

Schneider Electric Automation GmbH

Schneiderplatz 1
Marktheidenfeld, 97828 Germany

E316433

View model for additional information

Accessory Open type, Model(s): [TM3XREC1](#), [TM3XTRA1](#), [TM4ES4](#), [TM4PDPS1](#), [TMC4AI2](#), [TMC4AQ2](#), [TMC4HOIS01](#), [TMC4PACK01](#), [TMC4TI2](#)

FC6A Series CPU modules, Model(s): [TM221M16R](#), [TM221M16RG](#), [TM221M16T](#), [TM221M32TK](#), [TM221ME16R](#), [TM221ME16RG](#), [TM221ME16T](#), [TM221ME16TG](#), [TM221ME32TK](#)

FC6A Series I/O mixture moduels, Model(s): [TM3DM24R](#), [TM3DM24RG](#)

FC6A Series I/O mixture modules, Model(s): [TM3DM8R](#), [TM3DM8RG](#), [TM3XTYS4](#)

FC6A Series input modules, Model(s): [TM3DI16](#), [TM3DI16G](#), [TM3DI16K](#), [TM3DI32K](#), [TM3DI8](#), [TM3DI8A](#), [TM3DI8AG](#), [TM3DI8G](#)

FC6A Series output modules, Model(s): [TM3DQ16R](#), [TM3DQ16RG](#), [TM3DQ16T](#), [TM3DQ16TG](#), [TM3DQ16TK](#), [TM3DQ16U](#), [TM3DQ16UG](#), [TM3DQ16UK](#), [TM3DQ32TK](#), [TM3DQ32UK](#), [TM3DQ8R](#), [TM3DQ8RG](#), [TM3DQ8T](#), [TM3DQ8TG](#), [TM3DQ8U](#), [TM3DQ8UG](#)

FC6A Sieres CPU modules, Model(s): [TM221M16TG](#)

Listed accessories, communication modules, Model(s): [VW3E704+ Series](#)

Millenium 3 industrial programmable logic controllers, Model(s): [88 970 250](#), [88 970 270](#), [88 970](#), may be followed by [800 to 899](#), [88 972 250](#), [88 972 270](#), [88 974 250](#), [88 974 270](#), [88 974](#), may be followed by [800 to 899](#)

Millenium 3 industrial programmable logic controllers, Model(s): [88 970](#) followed by 0 thru 3, followed by 0 thru 6, followed by 0 thru 9.

Millenium 3 industrial programmable logic controllers, Model(s): [88 974](#) followed by 0 thru 3, followed by 0 thru 6, followed by 0 thru 9.

Open type, Programmable controllers, Model(s): [TM241C24R](#), [TM241C24T](#), [TM241C24U](#), [TM241C40R](#), [TM241C40T](#), [TM241C40U](#), [TM241CE24R](#), [TM241CE24T](#), [TM241CE24U](#), [TM241CE40R](#), [TM241CE40T](#), [TM241CE40U](#), [TM241CEC24R](#), [TM241CEC24T](#), [TM241CEC24U](#), [TM251MDESE](#), [TM251MESC](#), [TM251MESE](#)

Open type, Programmable controllers, Model(s): [TM3 followed by alphanumeric characters](#) Cat. Nos. [TM3AI8C](#), [TM3AQ4C](#), [TM3AM6C](#), [TM3AI8CG](#), [TM3AQ4CG](#), [TM3AM6CG](#).

Open type, Programmable controllers, "FC6A Series Analag Modules", Model(s): [TM3AI2H](#), [TM3AI2HG](#), [TM3AI4](#), [TM3AI4G](#), [TM3AI8](#), [TM3AI8G](#), [TM3AM6](#), [TM3AM6G](#), [TM3AQ2](#), [TM3AQ2G](#), [TM3AQ4](#), [TM3AQ4G](#), [TM3TI4](#), [TM3TI4D](#), [TM3TI4DG](#), [TM3TI4G](#), [TM3TI8T](#), [TM3TI8TG](#), [TM3TM3](#), [TM3TM3G](#), [TM3XPID2](#)

Open type, Programmable controllers, "FC6A Series CPU Modules", Model(s): [TM221C16R](#), [TM221C16T](#), [TM221C16TS01](#), [TM221C16U](#), [TM221C24R](#), [TM221C24T](#), [TM221C24U](#), [TM221C40R](#), [TM221C40T](#), [TM221C40U](#), [TM221CE16R](#), [TM221CE16T](#), [TM221CE16U](#), [TM221CE24R](#), [TM221CE24T](#), [TM221CE24U](#), [TM221CE40R](#), [TM221CE40T](#), [TM221CE40U](#)

Open type, Programmable controllers, "FC6A Series Option Modules", Model(s): [TMC2AI2](#), [TMC2AQ2C](#), [TMC2AQ2V](#), [TMC2CONV01](#), [TMC2HOIS01](#), [TMC2PACK01](#), [TMC2SL1](#), [TMC2TI2](#)

Open type, Programmable controllers, "TM3S series", Model(s): [TM3](#) followed by S, followed by AC, AF, AFL, and AK, followed by 5 or 6, followed by R, followed by G or Blank.

Programmable controllers, Model(s): [ABE-7 \(miniature\)](#), [ABE7 \(Twidofast\)](#), [ABE-7](#), [ABR-7](#), [ABS-7](#), [ABE-8](#), [ASI20M](#), [ASI67](#), [KT10659](#), [TWDNADK70P](#), [TM2](#), [TM238](#), [TM200](#)

Programmable Controllers, Model(s): [BT-4/DIO1-VBO04](#), [TM262L01MDESE8T](#), [TM262L01MESE8T](#), [TM262L10MESE8T](#), [TM262L20MESE8T](#), [TM262M05MESS8T](#), [TM262M15MESS8T](#), [TM262M25MESS8T](#), [TM262M35MESS8T](#), [TM3BCCO](#), [TM3BCEIP](#), [TM3BCSL](#), [TM3XFHSC202](#), [TM3XFHSC202G](#), [TM3XHSC202](#), [TM3XHSC202G](#), [TMSCO1](#), [TMSES4](#), [XPSMCMAI0200](#), [XPSMCMAI0200G](#), [XPSMCMAI0400](#), [XPSMCMAI0400G](#), [XPSMCMC10804](#), [XPSMCMC10804B](#), [XPSMCMC10804BE](#), [XPSMCMC10804BEG](#), [XPSMCMC10804BG](#), [XPSMCMC10804E](#), [XPSMCMC10804EG](#), [XPSMCMC10804G](#), [XPSMCMCB1604SA](#), [XPSMCMCB1604SAG](#), [XPSMCMCO00002EI](#), [XPSMCMCO0000CO](#), [XPSMCMCO0000COG](#), [XPSMCMCO0000DN](#), [XPSMCMCO0000DNG](#), [XPSMCMCO0000E](#), [XPSMCMCO0000EC](#), [XPSMCMCO0000ECG](#), [XPSMCMCO0000EG](#), [XPSMCMCO0000EI](#), [XPSMCMCO0000EIG](#), [XPSMCMCO0000EM](#), [XPSMCMCO0000EMG](#), [XPSMCMCO0000EP](#), [XPSMCMCO0000EPG](#), [XPSMCMCO0000MB](#), [XPSMCMCO0000MBG](#), [XPSMCMCO0000PB](#), [XPSMCMCO0000PBG](#), [XPSMCMCO0000S1](#), [XPSMCMCO0000S1G](#), [XPSMCMCO0000S2](#), [XPSMCMCO0000S2G](#), [XPSMCMCO0000UB](#), [XPSMCMCO0000UBG](#), [XPSMCMCO0002EIG](#), [XPSMCMCP0802](#), [XPSMCMCP0802BC](#), [XPSMCMCP0802BCG](#), [XPSMCMCP0802G](#), [XPSMCMDI0800](#), [XPSMCMDI0800G](#), [XPSMCMDI1200MT](#), [XPSMCMDI1200MTG](#), [XPSMCMDI1600](#), [XPSMCMDI1600G](#), [XPSMCMDO0002](#), [XPSMCMDO0002G](#), [XPSMCMDO0004](#), [XPSMCMDO00042A](#), [XPSMCMDO00042AG](#), [XPSMCMDO0004G](#), [XPSMCMDO0008C1](#), [XPSMCMDO0008C1G](#), [XPSMCMDO0016C1](#), [XPSMCMDO0016C1G](#), [XPSMCMEN0100HT](#), [XPSMCMEN0100HTG](#), [XPSMCMEN0100SC](#), [XPSMCMEN0100SCG](#), [XPSMCMEN0100TT](#), [XPSMCMEN0100TTG](#), [XPSMCMEN0200](#), [XPSMCMEN0200G](#), [XPSMCMEN0200HT](#), [XPSMCMEN0200HTG](#), [XPSMCMEN0200SC](#), [XPSMCMEN0200SCG](#), [XPSMCMEN0200TT](#), [XPSMCMEN0200TTG](#), [XPSMCMER0002](#), [XPSMCMER0002G](#), [XPSMCMER0004](#), [XPSMCMER0004G](#), [XPSMCMER0008](#), [XPSMCMER0008G](#), [XPSMCMMX0802](#), [XPSMCMMX0802G](#), [XPSMCMMX0804](#), [XPSMCMMX0804G](#), [XPSMCMRO0004](#), [XPSMCMRO0004DA](#), [XPSMCMRO0004DAG](#), [XPSMCMRO0004G](#)

Programmable controllers, "QUICKKEY", Model(s): [USB Memory Key - Cat. No. TM2USBABDEV1](#)

Programmable Controllers, "TM241C series", Model(s): [TM241C24R](#), [TM241C40R](#), [TM241CE24R](#), [TM241CE40R](#), [TM241CEC24R](#)

Servo motor drives, Model(s): [LMC](#) followed by 0, 1 or 2, followed by 00C, 01C, 06C, 12C, 16C, or 78C, may be followed by additional suffixes

Zelio logic industrial control programmable logic controllers, Model(s): [SR2 CBL08*](#)

Zelio logic industrial programmable logic controllers, Model(s): [SR2 BTC01*](#), [SR2 CBL01*](#), [SR2 CBL07*](#), [SR2 COM01*](#), [SR2 MEM01*](#), [SR2 MEM02*](#), [SR2 USB01*](#), [SR3 MBU01BD*](#), [SR3 NET01BD*](#)

Zelio logic industrial programmable logic controllers, Model(s): [SR2](#) followed by A, B, D, E or XT, followed by 4, 6, 10, 12, 14, 20 or 26, followed by 1, 2 or 3, followed by E, JD, B, BD or FU.*

Zelio logic industrial programmable logic controllers, Model(s): [SR3](#) followed by A, B, D, E or XT, followed by 4, 6, 10, 12, 14, 20 or 26, followed by 1, 2 or 3, followed by E, JD, B, BD or FU.*

* - May be followed by SP, followed by 001 thru 999.

+ - May be followed by suffixes.

NOTE - Models may include additional suffix(s) or different digit(s) substituting the letters and numbers "x" in the last positions to indicate software change or model variations

Last Updated on 2024-05-09

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."