



by Schneider Electric

Basic Rack PDU (AP9551)


Overview

The APC by Schneider Electric Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has fourteen NEMA 5-15R outlets.

Power cord. The 3.66-m (12-ft) power cord terminates with a NEMA L5-20P plug.

Circuit breaker. When the button is raised, the circuit breaker has tripped and the Rack PDU is overloaded, and at least one piece of equipment needs to be unplugged. The circuit breaker is rated to trip at 20 A.



Specifications

Electrical

Input connector	NEMA L5-20P plug
Output connectors	Fourteen NEMA 5-15R outlets
Nominal input voltage	100–120 VAC
Acceptable input voltage	±10% of nominal
Maximum input current	16 A (derated)
Input frequency	50/60 Hz

Physical

Dimensions (H x W x D)	610 x 42 x 44 mm (24.00 x 1.67 x 1.75 in)
Shipping dimensions (H x W x D)	648 x 178 x 152 mm (25.50 x 7.00 x 6.00 in)
Weight	2.20 kg (4.82 lb)
Shipping weight	2.92 kg (6.40 lb)

Environmental

Maximum elevation (above MSL)	
Operating	0 to 3 000 m (0 to 10,000 ft)
Storage	0 to 15 000 m (0 to 50,000 ft)
Temperature	
Operating	0 to 45°C (32 to 113°F)
Storage	-25 to 65°C (-13 to 149°F)
Humidity	
Operating	0 to 95% RH, non-condensing
Storage	0 to 95% RH, non-condensing

Compliance

Safety approvals	cULus Listed
------------------	--------------

Customer support and warranty information is available at www.apc.com.

© 2021 APC by Schneider Electric. All Rights Reserved.