

# Galaxy VM

The trusted partner for your business continuity 160-200 kVA (400 V)



se.com/ups



### High performance, low total cost of ownership

Galaxy VM is a highly efficient, easy-to-deploy, 160-200 kVA (400 V) 3-phase uninterruptible power supply (UPS) that seamlessly integrates into the electrical, physical, and monitoring environments of customers' medium data centers, industrial, or facilities applications.

Galaxy VM lowers your energy costs with up to 99% efficiency in eConversion mode and up to 96.5% efficiency in double conversion mode, and it seamlessly integrates into your electrical network with exceptional electrical performance.

Compliance with smart grid requirements makes Galaxy VM your partner in business profitability. Optimize your return on investment, and increase your UPS and energy storage utilization, with dispatchable operation. Galaxy VM also delivers flexible battery solutions, including modular and classic VRLA batteries as well as compatibility with Lithium-ion and NiCad batteries.

Galaxy VM is EcoStruxure<sup>™</sup> enabled, giving you visibility into the health of your UPS and peace of mind by sending real-time status updates directly to your smartphone. Designed for straightforward integration into any electrical network, Galaxy VM is the ideal choice to protect your critical infrastructure and your operating budget.



# Key advantages and innovations



#### 99% efficient in patented eConversion mode

Recover your initial investment within two-to-three years through energy savings.



#### Patented hybrid technology

Provides up to 96.5% efficiency in double conversion mode.

Maximum availability thanks to

Critical system components built as modules

redundancy and scalability options available.

for faster serviceability and fault tolerance. N+1

modular architecture



#### Grid interactive solution

Maximize savings, generate revenue, and improve resiliency by dispatching stored battery capacity or deploying fast frequency reserve support.

\* Contact your local representative for availability.



#### EcoStruxure IT

Monitor, manage, and model your IT infrastructure, and get service support, anytime, anywhere.\*

Battery flexibility, including

Increase availability and reduce

Total Cost of Ownership (TCO) with long-life, intelligent energy storage.

Lithium-ion batteries\*

#### Well-suited for a wide range of data center and industrial applications



#### Information technology and commercial buildings

- Medium and large data centers
- Computer rooms
- Retail/office space
- Manufacturing facilities

#### Healthcare

- Radiology and imaging equipment
- Operating rooms and Intensive Care Units
- Emergency power systems



#### Oil & gas

- Refining
- Petrochemicals
- Gas processing control Well pumps







#### **Transportation**

- Liahtina
- Air traffic control
- Security
- Signaling and communication systems


#### Minerals, Metals & Mining

- Furnace process control
- Glass plants
- **Emergency lighting**

#### **Power & Grid**


- Thermal plants
- Generator protection
- Hydro turbine control
- Wind farm monitoring

# Seamless integration and start-up



Distributed parallel connection for increased power and redundancy





#### Integration into your electrical network

- · Wide input voltage and frequency ranges
- Genset compliant with adaptive ramp-in
- Integrated parallel capability up to four UPS units
- Built-in integrated and tested back-feed protection

#### Integration with monitoring solutions

- Integrated network management capability for easy access to the network
- EcoStruxure connected; fully integrates into the comprehensive Schneider Electric<sup>™</sup> energy management solution for data centers and industrial applications
- Straightforward integration with facility infrastructure monitoring systems, including BMS and Modbus (SCADA and ION-E)

#### Smart power test

• Ability to test the UPS at full load without the need to rent a load bank and before bringing customers' load online.

#### Integration into your facility infrastructure

- Compact footprint
- · Back-to-the-wall installation
- Operates at 40 °C continuously without de-rating
- Embedded seismic design (OSHPD, IBC2012, and CBC2013 to Sds=2.02 g)
- Low audible noise levels
- · Replaceable dust filter for harsh environments
- · Configurable input/output relays
- Customizable dry contacts
- 7-inch touch-screen color display
- Top and bottom cable entry
- Parallel capability to increase multiple UPS systems for capacity or redundancy
- Ability to add UPSs in a parallel configuration without the need to transfer the load to bypass
- Cold start: capability to start the UPS on battery without mains power present
- External synchronization capability
- Parallel UPS configurations can be connected to a common battery without the need for a battery coupling cabinet, reducing footprint and increasing cost savings

### Premium protection and sustainability


eConversion: an unbeatable combination of power quality and high efficiency



#### Sustainably reduce your operating costs

Protect power to your load, reduce your total cost of ownership and electricity consumption, and meet your sustainability goals with up to 99% efficient, Class 1-compliant eConversion mode for Galaxy V-series UPSs, the recommended operating mode for your Galaxy V-series UPS.\*

- By operating at up to **99% efficiency**, the electricity savings in eConversion within 10 years typically equals **3x the price of the UPS**.
- The inverter operates continuously, protecting the load with **no transfer time**. eConversion performance has been certified with the same IEC 62040-3 **Class 1** rating as double conversion mode.
- eConversion mode recharges batteries and provides power factor correction and harmonics compensation, making it a versatile solution for IT and non-IT loads.
- Since its launch in 2014, eConversion has been successfully deployed all over the world. Join thousands of customers who use it daily to protect their critical loads.






Use our eConversion vs. Double Conversion Calculator to quickly assess your potential energy savings, operating cost optimization, and CO<sub>2</sub> emissions reduction by comparing the cost of running your Galaxy V-Series UPS in eConversion mode vs. double conversion mode.



Scan the QR code with your phone camera, or <u>click here</u> to access the calculator from the Schneider Electric Data Center Trade Off Tools<sup>™</sup> Web page.

#### Learn more about eConversion

\*Model dependent; based on a market electricity price: \$0.15 /kWh. The annual electricity savings are calculated by comparing the UPS efficiency in eConversion mode vs. double conversion mode.



# Flexible, intelligent energy storage

#### Modular battery string





#### Improved availability, including long-life options

- **Increased availability:** Four battery modules form one modular battery string. All battery modules support the load so no individual battery is a single point of failure
- Reduced Mean Time To Repair (MTTR): Replace a battery module in just a few minutes

#### Accurate anytime replacement

- Simple: Push-in and plug; unplug and pull-out
- Safety first: Touchproof connectors
- **Self-configuring:** The UPS automatically detects the presence and type of batteries so the battery configuration is updated accurately

#### Long-life Galaxy Lithium-ion batteries

As a first mover with a vast installed base, Schneider Electric has developed its own Galaxy Lithium-ion battery solution that also delivers these benefits:

- Double your battery life compared with any VRLA battery, optimizing TCO and achieving sustainability targets
- Recharge 2–3x faster than VRLA solutions
- High temperature tolerance
- Simplify and speed up installation with our internal power supply
- Enhance battery safety with three levels of battery management system (BMS)

#### Battery monitoring included

- **Sensors:** Each battery module contains two temperature sensors and a battery identification device for self-configuration
- **Runtime:** The estimate on the display interface updates when battery modules are removed or installed
- Quick status on display: Use the UPS display to quickly identify and replace an inoperative battery module

#### Flexible, high-density energy storage

- **Right-sizing:** Easily increase runtime by adding battery modules or installing battery cabinets
- **High density:** Integrate batteries in the UPS to reduce footprint. No need for service clearance between battery rows



#### **Classic VRLA batteries**

- Quickly install the battery cabinet
   next to the UPS
- Compact footprint



for Lithium-ion / VRLA battery comparison

# Grid Interactive Solution

### **Unlock the value of your UPS:** Maximize savings, generate revenue, and improve resiliency by dispatching stored battery capacity.

Lithium-ion batteries are increasingly being utilized to provide a variety of valuable grid services and generate steady income streams. With modern data centers leveraging Lithium-ion battery technology, such income streams are also available to data center owners. This added functionality enables quick return on investment while increasing system reliability and providing continuous state of health data.

- Participate in grid frequency stabilization
  - Reduce load on the grid by activating UPS storage
  - This Fast Frequency Reserve (FFR) program is available through the NORDEL grid in Norway, Finland, Sweden, and Denmark
- Increase system reliability
  - Improves overall performance by cycling batteries to validate their state of health
- Generate new revenue streams
  - Create additional revenue by participating in utility programs and electricity markets

Fast Frequency Reserve support

- Receive compensation for participating to grid frequency stabilization by discharging the UPS batteries
- Battery capacity: any (maximum demand: deliver 10-30 seconds of support)
- Region: Norway, Finland, Sweden, Denmark (DK2)
- Annual earnings: annual market auction (2021 prices were between 25k€ to 80k€ per MW)
- Annual full battery cycles (maximum): 5







### Maximize asset utilization by combining a dispatchable UPS and Lithium-ion batteries with EcoStruxure Microgrid Advisor (EMA)

Reduce risk with the Galaxy VM UPS platform while creating additional value, by dispatching lithium-ion batteries. The cloud-based EMA software platform automatically enables energy savings by optimizing loads with available resources, and can also enable a variety of other types of grid-supporting features, such as frequency support.



#### Galaxy VM UPS

- 24x7 power protection for mission-critical applications
- Modular power solutions for maximum flexibility and reliability
- Ultra-high efficiency, with eConversion operating mode to further reduce energy consumption
- Load protection and peace of mind even when dispatch functions are performed



#### Lithium-ion batteries

- High cycling capability, increased reliability, and longer life vs. lead-acid batteries
- High energy density allows for smaller footprint, translating to space savings
- Improved predictability and manageability via continuous battery monitoring
- Reduced TCO and simplified maintenance



#### EcoStruxure Microgrid Advisor

- Advanced model predictive control algorithms autonomously enable maximum energy savings while optimizing battery life
- Stay informed of energy usage, savings, and battery reserve via EMA app and Web site
- System reliability via 24-hour advanced automatic default operation schedules
- Cyber-secure platform to protect site and related data from external hacks.
- To learn more about EMA, visit: www.se.com/ema



To learn how much you can save or earn with this Grid Interactive Solution, contact your local Schneider Electric representative.

### **Options and accessories**



Battery cabinets



Classic battery cabinets



Wall-mounted battery breaker box



Modular battery cartridge



Dust filter kit

Included with Galaxy VM



Dry contact I/O accessory (AP9810)

• 6 configurable dry contacts IN

• 10 configurable dry contacts OUT

• 2 free slots for optional communication cards

Description	Protocol supported
1 plug: Ethernet SNMP	• HTTP, HTTPS, IPv4, IPv6, NTP, SMTP, SNMP v1,
<ul> <li>1 plug: RS485 modbus RTU</li> </ul>	SNMP v3, SSH V1, SSH V2, SSL, TCP/IP, Telnet,

and modbus RTU

Life is On | Schneider Electric 9


# Increase reliability and streamline deployment

Speed up deployment time, reduce start-up costs, and increase onsite reliability of the UPS operation by using the Smart Power Test (SPoT) mode before connecting your critical load.

#### **SPoT (Smart Power Test)**

SPoT enables the field service engineer (FSE) to test the UPS with full capacity current flow through important components and converters, without using a large system input current and without needing a load bank connected to the system or other system modifications.

- Simple, easy, and safe method to test the UPS at full power
- Can be conducted after service, repair, upgrade, or commissioning of UPS installation to verify system is properly installed
- Reduce risk to load and improve product quality
- Significant cost, time, and power savings





### Visibility and peace of mind

#### EcoStruxure IT enables resilient, secure, and sustainable data centers and IT environments

Schneider Electric's comprehensive Data Center Infrastructure Management (DCIM) solution, EcoStruxure IT, ensures business continuity by enabling secure monitoring, management, insights, planning, and modeling – whether from a single IT rack to hyper-scale IT – on-premises, in the cloud, and at the edge.









#### Easy visibility

Monitoring and management software streamlines data center device management:



**EcoStruxure IT Expert** provides you a hands-on approach with **cloud-based** monitoring software that synthesizes and analyzes performance and alert data into proactive recommendations and enables wherever-you-go visibility from any device. Try it now: <u>www.ecostruxureit.com/ecostruxure-itexpert/#trial</u>



**EcoStruxure Data Center Expert** is a scalable end-to-end **on-premise** monitoring software that collects, organizes, and distributes critical device information, providing a comprehensive view of your company-wide, multi-vendor physical infrastructure.

#### 24/7 peace of mind

Digital services proactively monitor your critical devices:



**EcoStruxure Asset Advisor**\* for secure power and cooling provides you a hands-off approach with 24/7 remote monitoring service by the Schneider Electric Connected Services Hub experts.

We monitor and troubleshoot, you relax.

#### Operations, optimized

Planning and modeling software transforms data into performance insights:



**EcoStruxure IT Advisor** is a data center infrastructure planning and modeling solution that provides Data Center Managers in large enterprises and colocation data centers with full insights into their infrastructure to improve profitability, sustainability, and resiliency.

#### Comprehensive on-site services

### Start-up service: included with UPS

 Commission the installation in accordance with manufacturer's recommendations. Ensure optimal system performance from Day 1

### Schneider Electric-certified installation services

 Expert configuration of your equipment for optimal performance and reliability

#### **Maintenance services**

- Ensure proper care of your mission-critical applications
- Preventive maintenance and response time upgrades, where available

#### Flexible service plans/ on-site extended warranty

- Hassle-free system maintenance
- Improve uptime at a predictable cost

\* Contact your local representative for availability.

## Technical specifications

Rated power (kVA/kW)	160/144 200/180											
Normal AC supply input												
Input voltage (V)	250-600 V											
Normal and bypass AC inputs				Single inpu	t or dual input	as standard						
Frequency (Hz)		40-70 Hz										
Input power factor		0.99										
THDI	< 3% full load											
Bypass AC input												
Input voltage range	342-457 V											
Frequency	50 Hz or 60 Hz											
Output												
Phase-to-phase output voltage (V)	380/400/415 V											
Load power factor	0.9 (0.7 leading to 0.5 lagging without de-rating)											
Output frequency	50/60 Hz +/- 0.1% (free-running)											
Overload capacity utility operation at 40 °C	150% for 1 minute and 125% for 10 minutes											
Output voltage regulation	+/- 1%											
Total harmonic distortion (THDU)	< 2% at 100% linear load; < 3% at 100% nonlinear load											
Output voltage tolerance	Symmetric load (0 – 100%): +/- 1% static; asymmetric load: +/- 3% static											
Overall efficiency												
eConversion mode (meets EN62040-3 Class 1)	Up to 99% (meets EN62040-3 Class 1)											
Efficiency at full load (AC-AC) at 100% load	Up to 96.5%											
Standard ECO mode	Up to 99%											
Communication and management												
Control panel	Multifunct	ion 7" touch-sc	reen color LCE	display with b	uilt-in NMC, m	odbus (SCADA	A and ION-E), tv	wo empty NM	C card slots			
Dimensions and weights												
UPS (H x W x D) mm	1970 x 1							1970 x 5260 x 854				
Weight in kg. (UPS) (total -power cabinet plus I/O cabinet)	699	724	1398	1448	2097	2172	2796	2896	3620			
Regulatory												
Safety	IEC 62040-1											
EMC/EMI/RFI	IEC 62040-2											
Markings	CE,C-Tick											
Performance	IEC 62040-3, VFI -SS -111											
Transportation	ISTA 2B											
Seismic zone	IBC Level 2:2006											
Environmental												
Operating temperature	0 to 40 °C											
Storage temperature	-25 to 55 °C without batteries -15 to 40 °C with batteries											
Relative humidity	0–95% non-condensing											
Operating elevation		1,000 m at 100% load										
Storage elevation					0–15,000 m							
Max. audible noise at 1 m from unit	55 dB at 70% load, 65 dB at 100% load											



To learn more about the the Galaxy VM UPS or EcoStruxure IT DCIM, contact your Schneider Electric representative or visit se.com/ups

**About Schneider Electric** At Schneider Electric, we believe access to energy and digital is a basic human right. We empower all to make the most of their energy and resources, ensuring Life Is On everywhere, for everyone, at every moment. We provide energy and automation digital solutions for efficiency and sustainability. We combine world-leading energy technologies, real-time automation, software and services into integrated solutions for Homes, Buildings, Data Centers, Infrastructure and Industries. We are committed to unleash the infinite possibilities of an open, global, innovative community that is passionate about our Meaningful Purpose, Inclusive and Empowered values. www.se.com

Schneider Electric SE 35 rue Joseph Monier 92500 Rueil Malmaison – France se.com

© 2023 Schneider Electric. All Rights Reserved. Schneider Electric | Life is On, EcoStruxure, Facility Expert, Facility Advisor are trademarks and the property of Schneider Electric SE, its subsidiaries and affiliated companies. • 998-22339634