

CARACTÉRISTIQUES TECHNIQUES / Technical data
VLVAF5N03517AB

TENSION ASSIGNEE / rated voltage (Un): 400 V
PUISSANCE ASSIGNEE / rated power (Qn): 350 Kvar
COURANT ASSIGNÉ / rated current (In): 505 A
COURANT MAXIMUM PERMANENT / maximum continuous current (Imp): 722 A

FRÉQUENCE ASSIGNÉE / rated frequency (Fn): 50 Hz
ISOLEMENT / insulation (Um): 690 V
PERTES CALCULÉES / calculated losses: 875 W
ACCORD / tuning: - Hz
COURANT ASSIGNE DE COURT-CIRCUIT CONDITIONNEL / rated
conditional short-circuit current (Icc): - kA
COURANT ASSIGNE DE COURTE DUREE ADMISSIBLE / rated short-time
withstand current (Icw): 35 kA/1s
UTILISATION INTÉRIEURE / indoor type: IP31
NORME / standard: IEC 61439-1 : 2011
IEC 61439-2 : 2011
IEC 61921 : 2017

TEMPERATURE / temperature: -5° / +45°C °C
MOYENNE SUR 24 HEURE / average temperature over 24 hours : 35°C °C
MOYENNE ANNUELLE / average annual temperature : 25°C °C

SCHEMA ELECTRIQUE DE PUISSANCE / Power diagram : PF5NA4S(S31)WOCBSPF
SCHEMA ELECTRIQUE DE CONTROLE / Control diagram : CF5NA4S(S31)WOCB
PLANS D'ARCHITECTURE, D'IMPLANTATION & D'INSTALLATION /
General Arrangement, Layout & Installation drawings : EF5NA4M4SBWOCBF
BORNIER CLIENT / Customer Terminal Blocks : S1B9989700



VarSet capacitor bank Auto 350kvar xxB 400V 50Hz

Number:

VLVAF5N03517AB

Revision:

00

Sheet:

1/2

Cette information est hautement confidentielle et elle est la propriété exclusive de Schneider Electric. Ce document ne doit pas être utilisé à d'autres fins que celles expressément permises par écrit par les propriétaires et ne doit pas être divulgué ou reproduit de quelque manière que ce soit sans la permission écrite des propriétaires.

The information is highly confidential and is the exclusive property of Schneider Electric copyright reserved. This document must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing.

NOMENCLATURE / Bill of material

Item	Description	Part N°
QS01	Gamme / range – Ref Disjoncteur / Ref Breaker	- - -
	Réglage / Setting	-
	Bobine MX - Auxiliary MX	-

MODULES						
	n=1	n=2	n=3	n=4	n=5	n=6
Power (kVar)	50	100	100	100	-	-
QS _n	Fuses 125A	Fuses 250A	Fuses 250A	Fuses 250A		
KM _n	LC1DWK12P7	LC1DWK12P7 x 2	LC1DWK12P7 x 2	LC1DWK12P7 x 2		
C _n	BLRCH500A000B40	BLRCH500A000B40 x 2	BLRCH500A000B40 x 2	BLRCH500A000B40 x 2		
DR _n	-	-	-	-		
	n=7	n=8	n=9	n=10	n=11	n=12
Power (kVar)	-	-	-	-	-	-
QS _n						
KM _n						
C _n						
DR _n						

Item	Description	Part N°
QF1	Fuses or CB	DF2CA04
QF2	Unipolar and neutral breaker	A9F74603
TC1	Transformer	ABL6TS63U
ST1	Thermostat (ventilation)	NSYCCOTH0
ST2	Thermostat (overheating)	NSYCCOTH0
EV1	Fan	NSYCVF575M230MF
EV2	Fan	
A1	PFC controller	VPL06N

(La liste et les références des composants figurant ci-après sont données à titre indicatif compte tenu de leur caractère évolutif du fait des éventuelles modifications de design ou évolutions des normes de référence / As product design and standards of reference change from time to time, the following list of part and corresponding reference are for information only)



VarSet capacitor bank Auto 350kvar xxB 400V 50Hz

Number:

VL VAF5N03517AB

Revision:

00


Sheet:

2/2


Cette information est hautement confidentielle et elle est la propriété exclusive de Schneider Electric. Ce document ne doit pas être utilisé à d'autres fins que celles expressément permises par écrit par les propriétaires et ne doit pas être divulgué ou reproduit de quelque manière que ce soit sans la permission écrite des propriétaires

The information is highly confidential and is the exclusive property of Schneider Electric copyright reserved. This document must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing.

A




B




C

GENIE CIVIL / CIVIL ENGINEERING




D





A


B

C

		Scale:	Technical Specification:		Units of measure : mm	
			Document Description:			
			DIMENSIONS GENIE CIVIL / CIVIL ENGINEERING DIMENSIONS			
			Document Number:		Doc. Rev.	Sheet:
			EF5NA4M4SBWOCBF		00	1 / 1
The information is highly confidential and is the exclusive property of Schneider Electric copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing. This drawing must be returned to the owners when the purpose has ceased.				State: Creation Printed on 2018/07/03		



- Connection not supply/Connexion non fournie



F55N auto P wiring diag W CB 4 steps

Schneider
Electric

Number:



PF5NA4S(S31)WOCBSPF


Revision:

1/1

All information and data contained in this document are the exclusive property of Schneider Electric Industries SAS and may neither be used nor disclosed without its prior written consent

State:




	Scale:	Tolerancing Standard :		Units of measure :	
	F5N CONTROL WIRING DIAGRAM - 4 STEPS - WITHOUT CB NETWORK : 400V-415V/50Hz & 400V/60Hz				
	Number:			Revision:	Sheet:
	CF5N4S(S31)WOCB			00	1 / 1
All information and data contained in this document are the exclusive property of Schneider Electric Industries SAS and may neither be used nor disclosed without its prior written consent			State:		

CUSTOMER TERMINAL BLOCK

Bornier client

Клеммный блок для внешних присоединений

VLVAW1N/VLVAW2N/VLVAW3N
/VLVAF5N/VLVAF6P
VLVAF2P/VLVAF3P/VLVAF5P



**

= 1 for VL6 VLVAW1N-VLVAW2N-VLVAW3N-VLVAF4P/
= 1 для контроллеров VL6 VLVAW1N-VLVAW2N-VLVAW3N-VLVAF4P
= 1 for VL12 VLVAF5N-VLVAF6P /
= 1 для контроллеров VL12 VLVAF5N-VLVAF6P

Измерение тока
Gen set/Groupe électrogène
Генераторная установка
PFC alarm/Alarme température
Сигнализация по температурному режиму
PFC current measure/Mesure courant régulateur
Alarm temperature information/Information alarme température
Сигнализация по температурному режиму



Scale:

Tolerancing Standard :

Units of measure :

Schneider
Electric

CUSTOMER TERMINAL BLOCKS
BORNIER CLIENT

Number: **S1B9989700**

Revision: **06** Sheet: **1 / 1**

All information and data contained in this document are the exclusive property of Schneider Electric.
Indicateurs SAE and may either be used or otherwise without the prior written consent.

State: