



Main

Device application	Distribution
Range	Acti9
Product name	Acti9 iK60
Product or component type	Miniature circuit-breaker
Device short name	iK60N
Poles description	4P
Number of protected poles	4
[In] rated current	32 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability for isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product certifications	SNI

Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 400 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 KV conforming to EN/IEC 60898-1
Contact position indicator	No
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	85 Mm
Width	72 Mm
Depth	78.5 Mm
Net weight	400 G
Colour	White
Mechanical durability	20000 Cycles

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Electrical durability	10000 Cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminal (top or bottom) 1...25 mm ² rigid Tunnel type terminal (top or bottom) 1...16 mm ² flexible
Wire stripping length	14 Mm for top or bottom connection
Tightening torque	2 N.M top or bottom
Earth-leakage protection	Without

Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 Cm
Package 1 Width	7.500 Cm
Package 1 Length	9.500 Cm
Package 1 Weight	404.000 G
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	8.500 Cm
Package 2 Width	10.000 Cm
Package 2 Length	22.000 Cm
Package 2 Weight	1.265 Kg
Unit Type of Package 3	S03
Number of Units in Package 3	33
Package 3 Height	30.000 Cm
Package 3 Width	30.000 Cm
Package 3 Length	40.000 Cm
Package 3 Weight	14.259 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**