



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**XB5EVM8**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**  
 Supply Voltage (Input): 230-240VAC 50/60Hz  
 Supply Voltage Limits: 195-264 VAC  
 Current Rating: 14mA  
 Surge Withstand: 1 kV conforming to IEC 61000-4-5  
 Bulb Type: Protected and Integrated LED  
 Ambient Air Temp. (for storage): -40°C to 70°C  
 Ambient Air Temp. (for operation): -25°C to 70°C  
 Conformity to Standards: EN/IEC 60947-1, EN/IEC 60947-5-1, UL508, CSA C22-2 n°14, IEC 61000-4-2, IEC 61000-4-3, IEC 6100-4-4, UL, FCC, CSA, CE

**Specification:**  
 Description: 22mm Monolithic Pilot light, complete, 230V, Yellow  
 Vibration Resistance: 5 gn (f=12...500 Hz) conforming to IEC 60068-2-6  
 Shock Resistance: 47 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27, 50 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27  
 IK degree of Protection: IK05 conforming to IEC 50102  
 Degree of Protection: IP66 conforming to IEC 60529, NEMA 4X, NEMA 13  
 Electric Service Life: 100,000 hours at rated voltage and at 25°C