



TERMINAL LUGS			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
30	#2	#14	AL
60	#2	#14	AL

KNOCKOUTS				
SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	44
E	1.50	38	2.00	51
F	2.00	51	2.50	64

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATING	AMPERE RATING	120 VAC		240 VAC				CORNER ③ GROUNDED DELTA SYSTEM		480 VAC				CORNER ③ GROUNDED DELTA SYSTEM		600 VAC				125 VDC ②		250 VDC ②		600 VDC ②	
			1PH		1PH		3PH				1PH ①		3PH				1PH ①		3PH							
			STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX	STD	MAX
DT321	240VAC;250VDC	30	.50	2	1.50	3	3	7.50	3	7.50	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	2	3	5		NA	NA
DT361	600VAC;600VDC	30	.50	2	1.50	3	3	7.50	3	7.50	3	7.50	5	15	5	15	3	10	7.50	20	2	3	5		10	15
DT322	240VAC;250VDC	60	1.50	3	3	10	7.50	15	7.50	15	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	5	10		NA	NA
DT362	600VAC;600VDC	60	1.50	3	3	10	7.50	15	7.50	15	5	20	15	30	15	30	10	25	15	50	NA	5	10		25	30

NOTES:
 UL LISTED - FILE E-2875
 CSA CERTIFIED - FILE #89067
 FINISH - GRAY BAKED ENAMEL.
 SHORT CIRCUIT CURRENT RATING:
 10,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS H OR K FUSES.
 200,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS J OR R FUSES.
 ① FOR SINGLE PHASE HP RATINGS USE 2 SWITCHING POLES.
 ② FOR DC RATINGS USE 2 SWITCHING POLES.
 ③ FOR CORNER GROUNDED DELTA SYSTEM, USE 2 SWITCHING POLES AND INSTALL NEUTRAL FOR GROUNDED CONDUCTOR.

HEAVY DUTY SAFETY SWITCH
 VISIBLE BLADES
 30 - 60 AMPERE
 ENCLOSURE - TYPE 1
 FUSIBLE



DWG# 3210C
NO.