

Sensor Solutions for Mobile Lift Applications



Telemecanique

Sensors

Simply easy!

> Telemecanique Sensors

Simply easy!

Simplicity



Proximity



Expertise



Telemecanique Sensors is a world-class global brand offering a comprehensive line of products with over 25,000 types of sensors, including limit switches, pressure sensors, photoelectric sensors and proximity sensors. In addition, we provide state-of-the-art RFID systems that are compatible with many PLC manufacturers.

Telemecanique Sensors has all the right agency approvals, such as UL, IEC, NEMA, CE, CCC, UL, CSA, and EAC.

Telemecanique Sensors is focused on three core values — Simplicity, Proximity, and Expertise. We have become experts in factory automation sensors as well as specialists in demanding applications, making our customers' lives "Simply easy!"

> Innovation focus



The new, software-configurable XXW54 Wide Beam Ultrasonic Sensor is a highly effective way to avoid mobile equipment collisions, both on the ground and when boom or scissor lift platforms rise into the air. The newly designed PCB of the sensor expands the width of the detection beam so it can cover a greater area.

Detection over a large coverage area



- Emits a beam with a 50° angle up to 1.5 meters.
- When conditions require multiple sensors installed in close proximity to each other, the 'synchronization' feature of the new XX Ultrasonic sensors allows reliable detection of objects from each sensor with minimal risk of cross-talk.

Detection of obstacles in harsh environments




- Anti-UV plastic housing allows operation in temperatures ranging from -40° C to +70° C.

Highly immune to electromagnetic interference



- The new XX Ultrasonic Sensors are E2-certified for mobile equipment. This entails a higher immunity to electromagnetic interference even in the most demanding environments.


> Truck loading cranes



- | | | |
|---|---|--|
| 1 | XCMV or XCMD Limit Switch | Compact body and modular head allows easy mechanical adaptation. |
| 2 | XMEP / XMLR / ZMLP Pressure Sensors / Monitor | Compact and robust for reliable operation. |
| 3 | XS SIL2 Inductive Sensor | Compact, robust, and increases level of safety. |
| 4 | XCKD Limit Switch & XCKZ05 Accessory | Robust for increased resistance to the operating environment. |
| 5 | XS Inductive Sensor | Easy installation and adjustment. |




> Garbage Trucks



- | | | |
|---|---------------------------|--|
| 1 | XUSL Light Curtains | Compact and robust for reliable operation. |
| 2 | XU2S Photoelectric Sensor | High levels of reliability and quality as well as long life duration. |
| 3 | 6 XG RFID Systems | Open for a free choice of electronic tags and networks. |
| 4 | XMEP Pressure Transmitter | Easy installation and adjustment. |
| 5 | 7 XS Inductive Sensors | Simple set-up and maintenance. |
| 8 | XX Ultrasonic Sensors | E2-certified for Mobile Equipment with better immunity against EMC interference. |




> Scissor Lift Platforms



- 1
XCMD Limit Switch & XCMZ06 Accessory
Compact and multitrack mounting for detecting the various heights.
- 2
XMEP Pressure Sensor
Compact and robust for reliable operation.
- 3
XCMV or XCKP Limit Switch
Compact, providing easy mechanical adaptation.
- 4
XXW54 Wide Beam Ultrasonic Sensors
E-certified with better immunity against EMC interference and a larger beam width.



> Boom Lift Platforms




- | | | | |
|---|------------------------------------|---------------------------|--|
| 1 | 4 | XCKP or XCMD Limit Switch | Compact body and modular head allows easy mechanical adaptation. |
| 2 | XCKP Limit Switch | | Compact, providing easy mechanical adaptation. |
| 3 | XXW54 Wide Beam Ultrasonic Sensors | | E-certified with better immunity against EMC interference and a larger beam width. |
| 5 | XMEP Pressure Transmitter | | Compact and robust for reliable operation. |
| 6 | XS Inductive Sensors | | Easy installation and adjustment. |
| 7 | XCMD Limit Switch | | The most compact Limit Switch body on the market with integrated connectors. |





Fork Lifts



- | | | |
|---|------------------------------------|--|
| 1 | XCKP or XCMD Limit Switch | Compact body and modular head allows easy mechanical adaptation. |
| 2 | XCMV Limit Switch | The most compact Limit Switch body on the market with integrated connectors. |
| 3 | XCMD Limit Switch | Compact body and a wide variety of heads for easier integration. |
| 4 | XMEP Pressure Sensor | Compaced and robust for reliable operation. |
| 5 | XS Inductive Sensor | Easy installation and adjustment. |
| 6 | XXW54 Wide Beam Ultrasonic Sensors | E-certified with better immunity against EMC interference and a larger beam width. |



> Choose product best-suited for your application

Limit switches

Product	Contact	Connection	Connection			Product	Connection	
			NO+NC Snap	NO+NC Slow	AMP 4P Connector		Deutsch DT04 4P Connector	
XCKD Metal	NO+NC Snap	1/2 NPT	XCKD2110N12	XCKD2102N12	XCKD2118N12	XCMD	Plunger	XCMD2110AM4 XCMD2510AM4
		M16	XCKD2110P16	XCKD2102P16	XCKD2118P16		Roller plunger	XCMD2102AM4 XCMD2502AM4
		Pg11	XCKD2110G11	XCKD2102G11	XCKD2118G11		Plastic roller lever	XCMD2115AM4 XCMD2515AM4
XCKP Plastic	NO+NC Snap	1/2 NPT	XCKP2110N12	XCKP2102N12	XCKP2118N12	XCMV	Plunger	XCMV2110D44 XCMV2510D44
		M16	XCKP2110P16	XCKP2102P16	XCKP2118P16		Roller plunger	XCMV2102D44 XCMV2502D44
		Deutsch	XCKP2110D44	XCKP2102D44	XCKP2118D44		Plastic roller lever	XCMV2115D44 XCMV2515D44
XCKT Plastic	NO+NC Snap	1/2 NPT	XCKT2110N12	XCKT2102N12	XCKT2118N12			
		M16	XCKT2110P16	XCKT2102P16	XCKT2118P16			
		Pg11	XCKT2110G11	XCKT2102G11	XCKT2118G11			
XCMD Metal	NO+NC Snap	1 m	XCMD2110L1	XCMD2102L1	XCMD2115L1			
	NO+NC Slow	1 m	XCMD2510L1	XCMD2502L1	XCMD2515L1			

Inductive sensors

Product	Sensing distance	Sensing distance					DC 3 wires NO	Sensing distance	
		4 mm	8 mm	5 mm	10 mm	15 mm		4 mm	8 mm
XS	cable	XS112B3PAL2	XS118B3PAL2	XS7F1A1PAL2	XS7E1A1PAL2	XS7C1A1PAL2	DC 3 wires NO+NC	XS112B3PCL2	XS118B3PCL2
	connector	XS112B3PAM12	XS118B3PAM12	XS7F1A1PAL01M8	XS7E1A1PAM8	XS7C1A1PAM8		XS112B3PCM12	XS118B3PCM12
NPN	cable	XS112B3NAL2	XS118B3NAL2	XS7F1A1NAL2	XS7E1A1NAL2	XS7C1A1NAL2			
	connector	XS112B3NAM12	XS118B3NAM12	XS7F1A1NAL01M8	XS7E1A1NAM8	XS7C1A1NAM8			



Pressure transmitters

Product	Connector	Analogue output	Pressure range					Display for XMEP
			0...60 bar	0...100 bar	0...250 bar	0...400 bar	0...600 bar	
XMEP	M12	0,5-4, 5V	XMEP060BD11F	XMEP100BD11F	XMEP250BD11F	XMEP400BD11F	XMEP600BD11F	PNP 2 switching outputs ZMLPA2P0SH
		4-20mA	XMEP060BD21F	XMEP100BD21F	XMEP250BD21F	XMEP400BD21F	XMEP600BD21F	
		0-10V	XMEP060BD71F	XMEP100BD71F	XMEP250BD71F	XMEP400BD71F	XMEP600BD71F	
Deutsch DT04-3P		0,5-4, 5V	XMEP060BT11F	XMEP100BT11F	XMEP250BT11F	XMEP400BT11F	XMEP600BT11F	PNP Analogue 4...20mA + 1 switching output ZMLPA2P0SH
		4-20mA	XMEP060BT21F	XMEP100BT21F	XMEP250BT21F	XMEP400BT21F	XMEP600BT21F	
		0-10V	XMEP060BT71F	XMEP100BT71F	XMEP250BT71F	XMEP400BT71F	XMEP600BT71F	
AMP Superseal 1,5 3-pin		0,5-4, 5V	XMEP060BV11F	XMEP100BV11F	XMEP250BV11F	XMEP400BV11F	XMEP600BV11F	
		4-20mA	XMEP060BV21F	XMEP100BV21F	XMEP250BV21F	XMEP400BV21F	XMEP600BV21F	
		0-10V	XMEP060BV71F	XMEP100BV71F	XMEP250BV71F	XMEP400BV71F	XMEP600BV71F	
XMLR	2 switching outputs	Analogue 4...20mA + 1 switching output	0...100 bar	0...160 bar	0...250 bar	0...400 bar	0...600 bar	ZMLPA2P0SH
			XMLR100M2P05	XMLR160M2P05	XMLR250M2P05	XMLR400M2P05	XMLR600M2P05	
			XMLR100M1P05	XMLR160M1P05	XMLR250M1P05	XMLR400M1P05	XMLR600M1P05	

Ultrasonic Sensors

Product	Sensing Distance	Analogue Output	Digital output	Connection		Reference Number
				0.15 cable + 6-pin Deutsch male connector	0.5M cable	
XXW54P3HPL01DM6	3m	0,5 - 4,5 V	PNP	0.15 cable + 6-pin Deutsch male connector	0.5M cable	XXW54P3HPL05
	1m Adjustable	n/a	PNP	5-pin M12 male connector		XXS18S1PM12
		4-20mA	n/a			XXS18S1AM12

Discover our complete offer: www.tesensors.com or contact your local sales agency

TMSS France

SAS au capital de 366 931 214,00€
2 AV GAMBETTA 92400
COURBEVOIE – France
908 125 255 RCS de Nanterre

www.tesensors.com

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TMSS France nor any of its subsidiaries or other affiliated companies shall be responsible or liable for misuse of the information contained herein.

TelemecaniqueTM Sensors is a trademark of Schneider Electric Industries SAS used under license by TMSS France. Any other brands or trademarks referred to in this document are property of TMSS France or, as the case may be, of its subsidiaries or other affiliated companies. All other brands are trademarks of their respective owners.

April, 2024

9006BR1103 R04/24