



## Basic Rack PDU


### Overview

The APC Basic Rack PDU distributes power to devices in the rack.

**Outlets.** The Rack PDU has twenty (20) IEC-320-C13 outlets, and four (4) IEC-320-C19 outlets.

**Power cord.** The 10-foot (3.05-meter) power cord terminates with an IEC-320-C20 connector.

### AP7552



## Specifications for AP7552

### Electrical

Input connector	IEC-320-C20 plug
Output connectors	(20) IEC-320-C13 (4) IEC-320-C19 outlets
Nominal input voltage	230 VAC
Acceptable input voltage	± 10% of nominal voltage
Input frequency	47–63 Hz
Cord length	10 ft (3.05 m)

### Physical

Dimensions (H × W × D)	63.75 × 2.19 × 1.73 in (161.92 × 5.56 × 4.39 cm)
Shipping dimensions (H × W × D)	84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.7 cm)
Weight	9.5 lb (4.3 kg)
Shipping weight	17 lb (7.7 kg)

### Environmental

Maximum elevation (above MSL)	
Operating	15,000 ft (4500 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	–5 to 45 °C (23 to 115 °F)
Storage	–25 to 65 °C (–13 to 149 °F)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

### Compliance

Safety verification	UL-EU, CE, RCM, EAC, KC, UKCA
---------------------	-------------------------------