



Main

Range	Acti9
Product name	Acti9 iDPN Vigi
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	iDPN N Vigi
Device application	Distribution
Poles description	1P + N
Number of protected poles	1
Neutral position	Left
[In] rated current	20 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Breaking capacity	6000 A Icn at 230...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	230...240 V AC 50 Hz
Magnetic tripping limit	5...10 x In
Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 230...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Rated breaking and making capacity	I _{dm} 6000 A at 230...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Limitation class	3 conforming to EN/IEC 61009-2-1
[Ui] rated insulation voltage	400 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
Connection pitch	9 Mm between phase and neutral

9 mm pitches	4
Height	85 Mm
Width	36 Mm
Depth	73 Mm
Product weight	125 G
Colour	White
Mechanical durability	20000 Cycles
Electrical durability	20000 Cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom 1...16 mm ² rigid Single terminal top or bottom 1...10 mm ² flexible Single terminal top or bottom 1...10 mm ² flexible with ferrule
Wire stripping length	15 Mm for top or bottom connection
Tightening torque	2 N.M top or bottom
Earth-leakage protection	Integrated


Environment

Standards	EN/IEC 61009-2-1
Product certifications	VDE[RETURN]GOST
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-2-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 Cm
Package 1 Width	8 Cm
Package 1 Length	10 Cm
Package 1 Weight	206 G
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9 Cm
Package 2 Width	11 Cm
Package 2 Length	25.5 Cm
Package 2 Weight	1.297 Kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	12.246 Kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	No
SCIP Number	Ed70c451-eb98-4beb-bfa0-d83cf974f40d
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg CO2 eq, Total Life cycle)	23

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------