


Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BMH1901P32F2A**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm): 190  
 Degree of Protection (Shaft / housing): IP65 / I P65  
 Maximum Current (Arms): 89.6  
 Holding brake: Yes  
 Encoder Type: ABS Multi turn 128 Sin/Cos period  
 Torque Constant (Nm/A): 1.3  
 CSA: Yes  
 RoHS: Yes  
 Weight without brake (kg / lb): 41.89 / 19

Specification:

Description:  
 Family: BMH  
 Maximum Permissible Speed (rpm): 4000  
 Continuous Stall Torque (Nm / lbs-in): 30 / 265.5  
 Peak Torque (Nm / lbs-in): 90 / 796.6