



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Uninterruptible power supply (UPS)
Battery type	Lead-acid battery

Complementary

Input voltage	230 V AC
Output voltage	230 V AC
Transfer time	6 ms typical : 10 ms maximum
Power range	1000 VA 600 W
Electrical connection	Input: 1 inlet IEC 320 C14 Output: 6 outlet IEC 320 C13
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Charging time	8 H
Battery voltage	12 V
Battery capacity	9.0 Ah
Net weight	5.7 Kg
Height	92.5 Mm
Width	160.5 Mm
Depth	305 Mm

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product certifications	CE

Physical

Mounting support	Wall Floor
------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.200 Cm
Package 1 Width	12.500 Cm
Package 1 Length	30.500 Cm
Package 1 Weight	5.702 Kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.000 Cm
Package 2 Width	40.000 Cm
Package 2 Length	60.000 Cm
Package 2 Weight	23.458 Kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	90.000 Cm
Package 3 Width	80.000 Cm
Package 3 Length	120.000 Cm
Package 3 Weight	199.664 Kg
SCC14	10731304338380

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years
----------	---------

Product Life Status : **Commercialised**