




| | | | |
|---|--|--------------------------|----------------------|
| | Scale: NTS | Technical Specification: | Units of measure: in |
| | Document Description: APVHU364NSSGL_CUSTOMER-DRAWING | | |
| Document Number: APVHU364NSSGL_CUSTOMER-DRAWING | | Doc. Rev. 00 | Sheet: 1/3 |
| <small>The information is highly confidential and is the exclusive property of Schneider Electric. It is not to be disclosed or reproduced in any way without permission from the Schneider Electric. This drawing must not be used for any purpose other than that expressly permitted in writing to the recipient and may not be disclosed or reproduced in any way without permission from the Schneider Electric. This drawing must not be used for any purpose other than that expressly permitted in writing to the recipient and may not be disclosed or reproduced in any way without permission from the Schneider Electric.</small> | | | Provisional |



3.02 [76.6] 1.88 [47.8] 3.65 [92.7] 1.88 [47.8]

12X Ø .50 [12.7]
12X Ø .32 [8.1]



| | | | |
|--|---|--------------------------|-------------------------|
| | Scale: NTS | Technical Specification: | Units of measure: in |
| | Document Description: APVHU364NSSGL_CUSTOMER-DRAWING | | Doc. Rev. Sheet: 00 2/3 |
| Document Number: APVHU364NSSGL_CUSTOMER-DRAWING | | State: | |

The information is highly confidential and is the exclusive property of Schneider Electric. Copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the issuer and may not be disclosed or reproduced in any way without permission from the issuer. A warning must be included in the legend when the drawing has closed.

| CATALOG NUMBER | VOLTAGE RATING | AMPERAGE RATING | AMPERAGE RATING |
|----------------|----------------|-----------------|-----------------|
| VHU364NSSGL | 600VAC/VDC | 200A | TYPE 4X |

| HORSEPOWER RATINGS | | | |
|--------------------|----|-----|-----|
| VOLTS | Ø | STD | MAX |
| *240V~ | 1 | -- | 15 |
| **240V~ | 3 | -- | 60 |
| *480V~ | 1 | -- | 50 |
| **480V~ | 3 | -- | 125 |
| *600V~ | 1 | -- | 50 |
| **600V~ | 3 | -- | 150 |
| *250V == | -- | 40 | -- |
| *600V == | -- | 50 | -- |

*USE ANY TWO SWITCHING POLES

**IF CORNER GROUNDED DELTA, USE OUTER SWITCHING POLES FOR UNGROUNDED CONDUCTORS


| ACCESORIES | | |
|-------------------------|-------------|---|
| KIT | VOLTAGE | PART NUMBER |
| ELECTRICAL INTERLOCK | 600V & 240V | EIK1, EIK2 |
| CLASS R FUSE KITS | 600V & 240V | HRK1020 |
| INTERNAL BARRIER | 600V & 240V | SS20 |
| SOLID NEUTRAL ASSEMBLY | 600V & 240V | SN20A for Al SN20C for Cu FOR CANADA: CSN20A for Al CSN20C for Cu |
| EQUIPMENT GROUNDING KIT | 600V & 240V | PKOGTA2 for Al PKOGTC2 for Cu |
| TOUCH UP PAINT | 600V & 240V | PK49SP |
| LOCK OFF/ON | 600V & 240V | LOGK2 |
| COPPER LUGS | 600V & 240V | CL20F |
| DOUBLE LUG | 600V & 240V | AL20DTF |
| COMPRESSION LUGS | 600V & 240V | VCELC030516H1 for Al VCELC030516H1 for Cu |

| Switch Rating (A) | Fuse or Circuit Breaker Type | 240VAC | 480VAC | 600VAC | 250VDC |
|--|------------------------------|--------|--------|--------|-------------|
| With upstream Fuse Protection | | | | | |
| ALL | H, K | 10 kA | 10 kA | 10 kA | Up to 10 kA |
| | R, T, J, L | 200 kA | 200 kA | 200 kA | |
| With Upstream Circuit Breaker Protection | | | | | |
| ALL | Any Brand Circuit Breaker | 10 kA | 10 kA | 10 kA | |
| 200A | PowerPact HD | 25 kA | 18 kA | 14 kA | Up to 10 kA |
| 200A | PowerPact HG | 65 kA | 35 kA | 18 kA | Up to 10 kA |
| 200A | PowerPact HJ | 65 kA | 35 kA | 25 kA | Up to 10 kA |
| 200A | PowerPact HL | 65 kA | 35 kA | 35 kA | Up to 10 kA |
| 200A | PowerPact HR | 65 kA | 35 kA | 35 kA | Up to 10 kA |
| 200A | FA | 14 kA | 14 kA | 14 kA | Up to 10 kA |
| 200A | FH | 18 kA | 18 kA | 18 kA | Up to 10 kA |

| Switch Rating (A) | Fuse or Circuit Breaker Type | 240VAC | 480VAC | 600Y/347 VAC | 250VDC |
|--|------------------------------|--------|--------|--------------|------------|
| With Upstream Circuit Breaker Protection | | | | | |
| 200A | PowerPact BD | 25 kA | 18 kA | 14 kA | Up to 10kA |
| 200A | PowerPact BG | 65 kA | 35 kA | 18 kA | Up to 10kA |
| 200A | PowerPact BJ & BK | 65 kA | 35 kA | 25 kA | Up to 10kA |

LINE SIDE

ACCEPTS: 6 AWG - 300 KCMIL (AL-CU)



LOAD SIDE

ACCEPTS: 6 AWG - 300 KCMIL (AL-CU)

NOTES:

FINISH - 316 STAINLESS STEEL

LUGS SUITABLE FOR 75°C AL-CU CONDUCTORS

SHORT CIRCUIT CURRENT RATINGS:

10,000 RMS SYMMETRICAL AMPERES WHEN USED IN CONJUNCTION WITH CLASS H OR K FUSES.
200,000 RMS SYMMETRICAL AMPERES WHEN USED IN CONJUNCTION WITH CLASS R, J OR T FUSES.
ON 600V SWITCHES, 100,000 AMPERES MAX ON CORNER GROUNDED DELTA WHEN PROTECTED BY CLASS J OR R FUSES, 200 AMPERE MAX.

cULus LISTED - FILE E2875

SEISMIC NOTES:

USE (4) 1/4" DIA GRADE 5 STEEL MOUNTING BOLTS AT SWITCH MOUNTING HOLES. MAX CONFIGURED WEIGHT 60 LB FOR THE PURPOSE OF DETERMINING SEISMIC ANCHORAGE REQUIREMENTS. FOR ALL OTHER APPLICATIONS, CONTACT SQUARE D COMPANY.

| | | | |
|---|--|--------------------------|----------------------|
| | Scale: NTS | Technical Specification: | Units of measure: in |
| | Document Description: APVHU364NSSGL_CUSTOMER-DRAWING | | |
| Document Number: APVHU364NSSGL_CUSTOMER-DRAWING | | Doc. Rev. 00 | Sheet: 3/3 |