

Basic Rack PDU


Overview

The American Power Conversion (APCTM) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has thirty (30) IEC-320-C13 outlets (15A maximum) and six (6) IEC-320-C19 outlets (16A maximum). APC power cord AP9877 (1.98 m; 6.5 ft) is available for purchase for use with C19 outlets.

Input power cord. The 3.05-m (10-ft) power cord terminates with a CS8365C connector.

AP7598



Electrical

Input connector	CS8365C plug
Output connectors	(30) IEC-320-C13 (6) IEC-320-C19 outlets
Cord length	3.05 m (10 ft)
Nominal input voltage	200-240 VAC, 3-phase
Acceptable input voltage	+6%, -10% of nominal voltage
Input frequency	50/60 Hz
Output current	15A/C13, 16A/C19; 16A/bank
Overload protection Internal External	(3) 20-A 2-pole breakers(1) 50-A 3-pole breaker
Physical	
Dimensions ($H \times W \times D$) (<i>Including breaker box</i>)	177.80×5.58×4.45 cm (70.00×2.20×1.75 in) 177.80×5.58×8.89 cm (70.00×2.20×3.50 in [†])
Shipping dimensions $(H \times W \times D)$	210.82×15.24×12.70 cm (83.00×6.00×5.00 in)
Weight	8.76 kg (19.33 lb)
Shipping weight	11.86 kg (26.16 lb)
Environmental	
Maximum elevation (above MSL) Operating Storage	3000 m (10,000 ft) 15 000 m (50,000 ft)
Temperature Operating Storage	-5 to 45° C (23 to 115° F) -25 to 65° C (-13 to 149° F)
Humidity Operating Storage	5–95% RH non-condensing 5–95% RH non-condensing
Regulatory Approvals	

Product safety	UL, cUL Listed

[†]The depth with the breaker box (89 mm; 35.0 in) extends for only a part (191 mm; 7.50 in) of the height of the unit.