



## Main

Range	Easy9
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	Easy9 RCBO
Poles description	1P + N
Neutral position	Left
[In] rated current	25 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Breaking capacity	4500 A Icn at 230 V AC 50 Hz conforming to IEC 61009-1

## Complementary

Device application	Distribution
Device location in system	Outgoer
[Ue] rated operational voltage	230 V AC 50 Hz
Magnetic tripping limit	5...10 x In
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Surge current	250 A
Contact position indicator	Yes
Control type	Toggle
Mounting support	DIN rail
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	66.5 mm
Colour	Grey (RAL 7035)
Mechanical durability	8000 Cycles
Electrical durability	2000 Cycles 230 AC 50 Hz
Connections - terminals	Tunnel type terminal (top or bottom) 1...25 mm <sup>2</sup> rigid Tunnel type terminal (top or bottom) 1...16 mm <sup>2</sup> flexible

Tightening torque	2 N.M top or bottom
Earth-leakage protection	Integrated

## Environment

Standards	IEC 61009-1
Product certifications	GOST[RETURN]EAC
Tropicalisation	2
Relative humidity	95 %
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.42 Cm
Package 1 Width	3.57 Cm
Package 1 Length	8.54 Cm
Package 1 Weight	194.0 G
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Height	30.0 Cm
Package 2 Width	30.0 Cm
Package 2 Length	40.0 Cm
Package 2 Weight	15.462 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**