

ADDITIONAL NOTES:



WHEN USED AS SERVICE EQUIPMENT, INSTALL BONDING STRAP AND REINSTALL GROUND LUG WHERE APPROPRIATE.

● HANDLE EXTENSION AVAILABLE M-FRAME BREAKER ORDER KIT 33195.

▲ THIS LUG IS AVAILABLE FROM SQUARE D. ORDER CATALOG NUMBER CMEK4, KIT INCLUDES 4 LUGS.

‡ INDICATED VERSA-CRIMP CRIMPING TOOL.

KNOCKOUTS		
SYMBOL	CONDUIT SIZE	
	IN	MM
A	.50	13
B	.75	19
E	1.50	38
F	2.00	51
G	2.50	64
H	3.00	76
I	3.50	89
J	4.00	102



DUAL DIMENSIONS: INCHES MILLIMETERS

CATALOG NUMBER	ALTERNATE LUG QUANTITY PER LINE SIDE PHASE AND NEUTRAL TERMINALS (ORDER SEPARATELY)							
	ANDERSON			ILSCO			CMC	
	VHCL-600-12BN	VHCL-750-12BN	LID2-600	2ACL-600	TA-600-2N▲	PB2-600-2N	A1B2-600-2	2AB2-600 (2-BARREL)
	250-600 CU	500-750 CU	#2-600 AL/CU	250-600 AL/CU	#2-600 AL/CU	(2)#2-600 AL/CU	#2-600 AL/CU	(2)#2-600 AL/CU
EZM3600CBU	2	2	2	2	2	2	2	1
EZM3800CBU	2	2	2	2	2	2	2	1

SYSTEM TYPE	MAIN RATING (AMPERES)	CATALOG NUMBER	MAIN CIRCUIT BREAKER (FACTORY INSTALLED)	LINE PHASE AND NEUTRAL LUG LANDING PADS PROVIDED FOR USE WITH CRIMP-TYPE LUGS(2-HOLE MOUNTING) QUANTITY OF LUGS PER PAD	GROUND LUG WIRE RANGE (FACTORY INSTALLED)
3Ø 4W 208Y/120VAC OR 240/120VAC DELTA	600	EZM3600CBU	MGF36600 (65kA) ●	2 (ORDER LUGS SEPARATELY)	(1) #6-300
	800	EZM3800CBU	MGF36800 (65kA) ●	2 (ORDER LUGS SEPARATELY)	(1) #6-300

NOTES:
 FINISH - GRAY BAKED ENAMEL POWDER COAT PAINT OVER CLEANED GALVANNEALED STEEL.
 UL LISTED - FILE E-10582, VOL. M, E-131840, VOL. M
 SUITABLE FOR USE AS SERVICE EQUIPMENT.
 MAIN HORIZONTAL CROSS BUS RATED 800A (ALUMINUM 1/4 X 1 3/4 INCHES TWO LAMINATIONS).
 MAIN DEVICES ARE SEALABLE BY UTILITY.
 GANGABLE MULTI-METERING EQUIPMENT IS DESIGNED FOR WALL MOUNTING ONLY
 (NOT SUITABLE FOR FLOOR STANDING EQUIPMENT).
 * MEETS EUSERC STANDARDS FOR WEST COAST BASED UTILITIES. DRAWING 315

EZ METER-PAK GANGABLE
 MULTI-METERING EQUIPMENT
 600A-800A 3PH 4W MAIN CIRCUIT BREAKER DEVICES
 UNDERGROUND FEED ONLY
 RAINPROOF TYPE 3R ENCLOSURES

by Schneider Electric

DWG# PWFDS-SYRS-0175
 NO.