


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH1402P27A2A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

| | |
|---|----------------------------------|
| Frame Size (mm): | 140 |
| Degree of Protection (Shaft / housing): | IP65 / I P65 |
| Maximum Current (Arms): | 57.42 |
| Holding brake: | No |
| Encoder Type: | ABS Multi turn 16 Sin/Cos period |
| Torque Constant (Nm/A): | 1.1 |
| CSA: | Yes |
| RoHS: | Yes |
| Weight without brake (kg / lb): | 23.46 / 12 |

Specification:

| | |
|--|--------------|
| Description: | BMH |
| Family: | 4000 |
| Maximum Permissible Speed (rpm): | 18.5 / 163.4 |
| Continuous Stall Torque (Nm / lbs-in): | 55.5 / 491.2 |
| Peak Torque (Nm / lbs-in): | |