



## Main

Range	TeSys
Product name	TeSys GC
Product or component type	Modular contactor
Device short name	GC63
Contactor application	Motor control Lighting Heating

## Complementary

Utilisation category	AC-7B AC-7A
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	$\leq 250$ V AC
[Ie] rated operational current	63 A AC-7A 25 A AC-7B
Operating position	30°/Vertical
Control circuit type	AC at 60 Hz
[Uc] control circuit voltage	220...240 V AC 60 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ith] conventional free air thermal current	63 A (at 50 °C) for power circuit
Irms rated making capacity	200 A at 400 V AC for power circuit conforming to IEC 61095
Rated breaking capacity	200 A at 400 V for power circuit conforming to IEC 61095
[Icw] rated short-time withstand current	504 A 40 °C - 10 s for power circuit 157 A 40 °C - 30 s for power circuit
Associated fuse rating	63 A gL at $\leq 440$ V for power circuit
Average impedance	2 MOhm - Ith 63 A 50 Hz for power circuit
[Ui] rated insulation voltage	500 V conforming to IEC 61095 500 V conforming to VDE 0110
Electrical durability	AC-7A: 100000 cycles AC-7B: 100000 cycles
Power dissipation per pole	8 W
Control type	Remote control
Mounting mode	Clip-on
Mounting support	DIN rail
Standards	IEC 60947-5 IEC 61095

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm <sup>2</sup> flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1.5 mm <sup>2</sup> solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> solid without cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm <sup>2</sup> flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 16 mm <sup>2</sup> flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 16 mm <sup>2</sup> flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 4 mm <sup>2</sup> flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm <sup>2</sup> solid without cable end Power circuit: screw clamp terminals 2 cable(s) 6 mm <sup>2</sup> solid without cable end
Tightening torque	Control circuit: 0.8 N.m - on screw clamp terminals Power circuit: 2 N.m - on screw clamp terminals
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 Cycles
Maximum operating rate	300 Cyc/H 50 °C
Control circuit voltage limits	Drop-out: 0.2...0.75 Uc at 50 Hz (at <50 °C) Operational: 0.85...1.1 Uc at 50 Hz (at <50 °C)
Inrush power in VA	53 VA 50 Hz (at 20 °C)
Hold-in power consumption in VA	6.5 VA 50 Hz (at 20 °C)
Heat dissipation	2.1 W at 50/60 Hz

## Environment

IP degree of protection	IP40 conforming to VDE 0106 (in enclosure) IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m
Mechanical robustness	Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz
Total number of 18 mm modules	3
Height	85 Mm
Width	54 Mm
Depth	62.5 Mm
Net weight	0.39 Kg
Quantity per set	Set of 4
Colour	White

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 Cm
Package 1 Width	9.5 Cm
Package 1 Length	23.0 Cm
Package 1 Weight	330.0 G
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	8.0 Cm
Package 2 Width	9.5 Cm
Package 2 Length	23.0 Cm
Package 2 Weight	1.322 Kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------