


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

HMIGTO5315



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

UL Certifications:	UL/c-UL Listed, (UL508)
CSA Certifications:	CSA-C22.2 No.142-M1987
ANSI/ISA Certifications:	ANSI/ISA 12.12.01
CE Markings:	CE EN61000-6-2, EN61000-6-4, EN61131-2
WEEE 2002/96/EC:	Yes
RoHS 2002/95/EC:	Yes
RoHS China SJ/T 11363-2006:	Yes
Common Automation Protocols:	Modbus, Uni-TE, FIPWAY, FIPIO, Modbus Plus
Other Protocols:	PacDrive, Siemens, Omron, Mitsubishi, Rockwell
Operating Temperature Range:	0°C (32°F) to 50°C (122°F)
Storage Temperature Range:	-20 to 60 °C [-4 to 140 °F]
Relative Humidity"	0 to 90% non-condensing

Specification:

Description:	Human Machine Interface GTO5315
Screen Type:	TFT Color LCD (10.4 inch)
Resolution:	640 x 480 pixels (QVGA)
Interface Ports:	RS-232C, RS-485 RJ45
Enclosure Rating:	IP66K, NEMA4x
USB Ports:	1 Type-A and 1 mini-B
RAM:	512kb SRAM with battery backup
Storage:	96MB App Flash
Supply Voltage:	24VDC ± 4.8