



DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
 INCOMPLETE COMPONENT – THE FINAL ACCEPTANCE OF THIS COMPONENT IS DEPENDANT UPON ITS INSTALLATION AND USE IN COMPLETE EQUIPMENT SUBMITTED TO UNDERWRITERS LABORATORIES, INC. OR CANADIAN STANDARDS ASSOCIATION
 UL RECOGNIZED COMPONENT FILE: E6294
 CSA PANELBOARD INTERIOR FILE: LL89066
 SUITABLE FOR USE WITH 75°C COPPER OR ALUMINUM MAIN CONDUCTORS. SEE BRANCH BREAKERS FOR BRANCH WIRE RATINGS.
 USE ONLY SQUARE D TYPE QO, QOA, QOC, QOP AND QOT (20A MAX. NON-CTL) BRANCH CIRCUIT BREAKERS. USE OF OTHERS VOIDS THE WARRANTY. MAY VOID THE UL LISTING AND MAY RESULT IN PROPERTY LOSS OR PERSONAL INJURY.
 SHORT CIRCUIT CURRENT RATING 10,000 RMS SYMMETRICAL AMPERES AT 240 VAC MAX.
 ADDITIONAL OR REPLACEMENT BRANCH CIRCUIT BREAKERS MUST HAVE AN INTERRUPTING RATING EQUAL TO OR GREATER THAN THAT OF THE CIRCUIT BREAKERS WITH THE LOWEST INTERRUPTING RATING PRESENTLY INSTALLED.
 MAXIMUM CONTINUOUS LOADS ON BRANCH CIRCUITS NOT TO EXCEED 80% OF THE RATINGS OF THE CIRCUIT BREAKERS EMPLOYED IN OTHER THAN MOTOR CIRCUITS.

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG/kcmil	NUMBER OF BRANCH NEUTRAL TERMINALS
					AL OR CU	
QON124L200PI	240 VAC	200	24	36	#4 – 250	41

QON124L200PI	SQUARE D by Schneider Electric
	DWG# MFR7032502 NO.