**UL-EU CERTIFICATE** 

Certificate No.	UL-EU-01957
Page	1/7
Date of Issue	2020-09-24
Certificate Holder	Schneider Electric IT Corporation, FKA APC American Power Conversion
	132 Fairgrounds Rd PO BOX 278
	West Kingston, RI 02892 USA
Manufacturer	Schneider Electric IT Corporation, FKA APC American Power Conversion
	132 Fairgrounds Rd PO BOX 278 West Kingston, RI 02892_USA
Production site	EAST INDIA TECHNOLOGIES PVT. LTD.
	Survey No. 17, Kammanahalli Village Bannerghatta Rd BANGALORE, Karnataka 560076 India
	See Page 2
Certified Product	Accessory, Power Distribution Unit - Single and Poly phase, for use in certified ITE.
Model	Basic Models: AP6003A, AP6007A, AP6009A, AP6015A See Page 2
Trademark	APC by Schneider Electric
ed Voltage / Frequency	See Page 2
Rated Current / Power	See Page2
Insulation Class	Class I
egree of protection (IP)	IPX0
Tested acc. to	EN 62368-1:2014/A11:2017, EN 62368-1:2014
Test Report No.	E177299-A6016-CB-1 issued on 2020-09-24
Additional	Stationary, rack-mounting.
Expire date	2030-09-24

Certification Manager Jan-Erik Storgaard UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonization of the laws of Member States relating to the marking available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate. The designated Oretificate holder is entitled to use the UL-EU Mark for the Certified Product manufactured at the production site(s)

The designated Certificate holder is entitled to use the UL-EU Mark for the Certified Product manufactured at the production site(s) identified above, in accordance with the UL-EU Mark Service Agreement, including without limitation the UL-EU Mark Testing and Certification Services Service Terms. Only those Products bearing the UL-EU Mark for Europe should be considered as being covered by UL's UL-EU Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard(s) identified on this Certificate is amended or withdrawn prior the expiration date.



www.ul.com

Certificate No. UL-EU-01957 Page 2/7 Date of Issue 2020-09-24

### Model Details:

AP6020A,AP6031A, AP6032A, AP6038A, AP6120A, AP9559, AP9565,AP9568, AP9572. Smart Models: AP7811B, AP7820B, AP7821B, AP7911B, AP7920B, AP7921B. Basic Models: AP7526 (EMEA ONLY), AP7551 (EMEA ONLY), AP7552 (EMEA ONLY), AP7553 (EMEA ONLY), AP7554 (EMEA ONLY), AP7555A (EMEA ONLY), AP7557 (EMEA ONLY). Smart Models: AP7822B (EMEA ONLY), AP7850B (EMEA ONLY), AP7922B (EMEA ONLY), AP7950B (EMEA ONLY).

Production Sites: SCHNEIDER ELECTRIC IT BUSINESS INDIA PVT LTD PLOT NO 73 SURVEY NO. 103, 2ND PHASE JIGANI INDUSTRIAL AREA BANGALORE, Karnataka 562106 India

SGS TEKNIKS MANUFACTURING PRIVATE LIMITED PLOT NO 211, JIGANI-BOMMASANDRA LINK ROAD INDUSTRIAL AREA, JIGANI, BANGALORE, Bengaluru (Bangalore) Rural, Karnataka 560106 India

Ratings: AP6003A Input: 100-240 VAC, 1~, 16A, 50/60 Hz Output: 100-240 VAC, 1~, 16A C13: 10A PER OUTLET

AP6007A Input: 200-240 VAC, 50/60Hz, 32A Output: 200-240 VAC, 16A PER BANK, 32A MAX C19: 13A PER OUTLET, 16A PER GROUP C13: 10A PER OUTLET, 16A PER GROUP

AP6009A Input: 200-240 VAC, 50/60Hz, 32A Output: 200-240 VAC, 32A MAX, 16A PER BANK C19: 16A PER OUTLET, 16A PER GROUP C13: 10A PER OUTLET, 16A PER GROUP AP6015A

> Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.



Certificate No. UL-EU-01957 Page 3/7 Date of Issue 2020-09-24

Ratings (Continue): AP6015A Input: 200-240 VAC, 1~, 10A, 50/60Hz Output: 200-240 VAC, 1~, 10A MAX C13: 10A PER OUTLET

### AP6020A

Input: 200-240 VAC, 1~, 16A, 50/60Hz Output: 200-240 VAC, 1~, 16A MAX C13: 10A PER OUTLET

#### AP6031A

Input: 200-240 VAC, 1~, 24A, 50/60Hz Output: 200-240 VAC, 1~, 30A MAX C19: 16A PER OUTLET

## AP6032A

Input: 200-240 VAC, 50/60Hz, 32A Output: 200-240 VAC, 32A MAX C19: 16A PER OUTLET 16A MAX PER BANK

### AP6038A

Input: 200-240 VAC, 1~, 50/60Hz, 48A Output: 200-240 VAC, 48A MAX C19: 16A PER OUTLET

#### AP6120A

Input: 200-240 VAC, 1~, 16A, 50/60Hz Output: 200-240 VAC C13: 10A PER OUTLET C19: 16A PER OUTLET

#### AP9559

Input:100-240 VAC,50/60Hz,16A Output: 100-240 VAC, 16A TOTAL 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

### AP9565

Input: 100-240 VAC, 50/60Hz, 16A Output: 100-240 VAC, 16A TOTAL 10A MAX PER C13 OUTLET

> Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.



Certificate No. UL-EU-01957 Page 4/7 Date of Issue 2020-09-24

Ratings (Continue): AP9568 Input: 100-240 VAC, 50/60Hz, 12A Output: 100-240 VAC,10A TOTAL 10A MAX PER C13 OUTLET

AP9572 Input: 100-240 VAC, 50/60Hz, 16A Output: 100-240 VAC, 16A TOTAL 10A MAX PER C13 OUTLET

AP7811B Input: 200-240 / 208 VAC, 50/60Hz, 24A Output: 200-240 / 208 VAC 24A MAX 16A MAX PER BANK 12A MAX PER IEC 320 C13 OUTLET 16A MAX PER IEC 320 C19 OUTLET

AP7820B Input: 100-240 VAC, 50/60Hz,10A Output: 100-240 VAC 10A MAX PER OUTLET

AP7921B Input:220-240 VAC, 50/60Hz,16A Output: 220-240 VAC, 16A TOTAL 10A MAX PER OUTLET

AP7526 (EMEA ONLY) Input: 220/380-240/415 VAC, 3W+N+PE, 32A, 50/60Hz Output: 220-240 VAC, 32A MAX C19: 16A PER OUTLET

AP7551 (EMEA ONLY) Input: 200-240/208 VAC, 50/60Hz,16A Output: 200-240 / 208 VAC, 16A TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

> Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.



Certificate No. UL-EU-01957 Page 5/7 Date of Issue 2020-09-24

Ratings (Continue): AP7552 (EMEA ONLY) Input: 200-240/208 VAC, 50/60Hz, 16A Output: 200-240/208 VAC, 16A TOTAL 16A MAX PER BANK

TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

AP7553 (EMEA ONLY) Input: 200-240/208 VAC, 50/60Hz, 32A Output: 200-240/208 VAC, 32A TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

AP7554 (EMEA ONLY) Input: 200-240/208 VAC, 50/60Hz, 16A Output: 200-240 /208 VAC, 16A TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

AP7555A (EMEA ONLY) Input: 220/380-240/415 VAC, 3W+N+PE, 32A Output: 220-240 VAC, 32A TOTAL 16A MAX PER OUTLET

AP7557 (EMEA ONLY) Input: 220/380-240/415 VAC, 3W+N+PE, 16A Output: 220-240 VAC, 16A TOTAL 16A MAX PER OUTLET

AP7822B (EMEA ONLY) Input: 220-240 VAC, 50/60Hz, 32A Output: 220-240 VAC, 32A TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET 16A MAX PER C19 OUTLET

> Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.



Certificate No. UL-EU-01957 Page 6/7 Date of Issue 2020-09-24

Ratings (Continue): AP7850B (EMEA ONLY) Input: 220-240 VAC, 50/60Hz, 10A Output: 220-240 VAC, 10A TOTAL 10A MAX PER C13 OUTLET

AP7922B (EMEA ONLY) Input: 220-240 VAC, 50/60Hz, 32A Output: 220-240VAC, 32A TOTAL 16A MAX PER BANK 10A MAX PER C13 OUTLET

AP7950B (EMEA ONLY) Input: 200-240/208 VAC, 50/60Hz, 10A Output: 200-240/208 VAC, 10A TOTAL 10A MAX PER BANK 10A MAX PER C13 OUTLET

AP7821B Input: 100-240 VAC, 50/60Hz, 16A MAX Output: 100-240 VAC 16A MAX TOTAL 10A MAX PER OUTLET

AP7911B Input: 240/208 VAC 50/60Hz, 24A Output: 200-240/208 VAC, 24A TOTAL 16A MAX PER BANK 12A MAX PER IEC 320 C13 OUTLET

AP7920B Input: 220-240 VAC, 50/60Hz, 10A Output: 220-240 VAC, 10A TOTAL 10A MAX PER OUTLET

> Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the marking available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex I" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.



 Certificate No.
 UL-EU-01957

 Page
 7/7

 Date of Issue
 2020-09-25

### **Certification Mark UL-EU Mark**

The UL-EU Mark, as displayed below, shall appear on certified products only. Minimum size is not specified, as long as the Mark is legible. The following is suggested.



The minimum height of the registered trademark symbol ® shall be 1 mm. When the overall diameter of the UL-EU Mark is less than 9.5 mm, the trademark symbol may be omitted if it is not legible to the naked eye.

The UL-EU Mark may appear on a label, nameplate, or may be cast, stamped or molded into the product. When appearing on a label or nameplate, the Manufacturer's name or trademark along with a model number are also required on that same label or nameplate. If cast, stamped or molded, the Certificate Manufacturer's name or trademark and model number shall also appear elsewhere on the product.

All content shall be in accordance with the details provided on this UL-EU Certificate.

## PROCUREMENT

The Production site may reproduce the Mark or obtain it from a UL authorized supplier. The list of UL authorized suppliers can be found on UL's online directory at www.ul.com

Certification Body UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found to have been in compliance with the above mentioned harmonized Standard(s) per Article 12 of Directive 2014/35/EU of the European Parliament of the Council of 26 February 2014 on the harmonisation of the laws of Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits, in accordance with the UL-EU Requirements. As stated in Article 6 of Directive 2014/35/EU, "When placing their electrical equipment on the market, manufacturers shall ensure that it has been designed and manufactured in accordance with the safety objectives referred to in Article 3 and set out in Annex II" and "Manufacturers shall draw up the technical documentation referred to in Annex III and carry out the conformity assessment procedure referred to in Annex III or have it carried out". These elements as well as declared compliance with 2014/35/EU remains the responsibility of the manufacturer and is not covered as part of this certificate.

