


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
SC300A500FP



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Sensing Window:
 Far Limit:
 Sensing Range:
 Circuit Type:
 Output Mode: Discrete
 Volts Type: DC
 Voltage Range: 12-24 VDC
 Max Load: 100 mA
 Current Consumption: 25 mA
 Sonic Frequency: 500 kHz
 Temp Range: -30° to 70° C (-22° to 158° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: IP67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Ultrasonic Sensor
 Description: Ultrasonic Sensor, Discrete, Flat Profile, 12-24 VDC
 Body Style: Flat Profile
 Diameter: 0
 Housing Material: Glass Epoxy
 Face Material: Yes, using AC441 Configurator and Superprox+ Software
 Field Configurable: Configurable
 Functionality: 3.0 m (10 ft)
 Cable Size: Flat profile
 Connector Type:
 Special Features: