



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

SM600AJ0L90AL



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Sensing Window: 29.5 mm (1.16 in)
 Far Limit: 88.9 mm (3.5 in)
 Sensing Range:
 Circuit Type: Normally Open
 Output Mode: NPN/PNP
 Volts Type: DC
 Voltage Range: 12-24 VDC
 Max Load: 100 mA
 Current Consumption: 50 mA
 Sonic Frequency: 500 Hz
 Temp Range: 0° to 60° C (32° to 140° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: IP67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Ultrasonic Sensor
 Description: Ultrasonic Sensor, Discrete, 18 mm Barrel, 12-24 VDC
 Body Style: Barrel
 Diameter: 18 mm
 Housing Material: 0
 Face Material: Silicone Rubber
 Field Configurable: No
 Functionality: Object Mode, Delayed Ramp, Extended Deadband, Narrow Transmit pulse
 Cable Size: 3.0 m (10 ft)
 Connector Type:
 Special Features: