



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**SM606A67400**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Sensing Window: 117.5 mm (4.63 in)  
 Far Limit: 152.4 mm (6.0 in)  
 Sensing Range:  
 Circuit Type:  
 Output Mode: Inverse 0 to 10 V  
 Volts Type: DC  
 Voltage Range: 15-24 VDC  
 Max Load: 1k ohm  
 Current Consumption: 50 mA  
 Sonic Frequency: 500 Hz  
 Temp Range: 0° to 60° C (32° to 140° F)  
 NEMA Type: 4X (indoor use only)  
 IP Rating: IP67  
 Standards: UL, CE Rohs

**Specification:**

Sensor Type: Ultrasonic Sensor  
 Description: Ultrasonic Sensor, Analog - Voltage (V), 18 mm Barrel, 15-24 VDC  
 Body Style: Barrel  
 Diameter: 18 mm  
 Housing Material: 0  
 Face Material: Silicone Rubber  
 Field Configurable: No  
 Functionality:  
 Cable Size: 3.0 m (10 ft)  
 Connector Type:  
 Special Features: