

DPE38G7

IEC contactor, Easy TeSys
DPE, nonreversing, 38A, 3P, 20HP at 480V
AC, 120V 50/60Hz coil



Product availability: Stock - Normally stocked in distribution facility

Price*: 71.25 USD



Main

Range	Easy TeSys
Product name	Easy TeSys DPE
Product or Component Type	Contacteur
Device short name	DPE
Contacteur application	Resistive load Motor control
Utilisation category	AC-4 AC-1 AC-3
Poles description	3P
Pole contact composition	3 NO
Auxiliary contact composition	1 NO
[Ie] rated operational current	38 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 52 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] control circuit voltage	120 V AC 50/60 Hz
Motor power kW	9 KW 220...230 V AC 50/60 Hz 18.5 KW 380...400 V AC 50/60 Hz 18.5 KW 415 V AC 50/60 Hz 18.5 KW 440 V AC 50/60 Hz 18.5 KW 500 V AC 50/60 Hz 18.5 KW 660...690 V AC 50/60 Hz
Maximum Horse Power Rating	2 Hp at 115 V AC 50/60 Hz for 1 phase motors 5 Hp at 230/240 V AC 50/60 Hz for 1 phase motors 10 Hp at 200/208 V AC 50/60 Hz for 3 phase motors 10 Hp at 230/240 V AC 50/60 Hz for 3 phase motors 20 Hp at 460/480 V AC 50/60 Hz for 3 phase motors 25 Hp at 575/600 V AC 50/60 Hz for 3 phase motors

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Complementary

[Ue] rated operational voltage	Power circuit ≤ 690 V AC 25...400 Hz Power circuit ≤ 300 V DC
[Ith] conventional free air thermal current	10 A (at 140 °F (60 °C)) for signalling circuit 50 A (at 140 °F (60 °C)) for power circuit
Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947
Rated breaking capacity	550 A at 440 V for power circuit conforming to IEC 60947
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at ≤ 690 V coordination type 1 for power circuit 63 A gG at ≤ 690 V coordination type 2 for power circuit
Average impedance	2 MOhm - Ith 50 A 50 Hz for power circuit
Power dissipation per pole	2 W AC-3 5 W AC-1
Electrical durability	1 Mcycles 38 A AC-3 ≤ 440 V 0.6 Mcycles 52 A AC-1 ≤ 440 V
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 2000000 cycles contactor with mechanical load EN/ISO 13849-1
Control circuit type	AC 50/60 Hz
Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.3...0.6 U _c at 50/60 Hz (at <158 °F (70 °C)) Operational: 0.8...1.1 U _c at 50 Hz (at <140 °F (60 °C)) Operational: 0.85...1.1 U _c at 60 Hz (at <140 °F (60 °C)) Operational: 1...1.1 U _c at 50/60 Hz (at <158 °F (70 °C))
Inrush power in VA	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-in power consumption in VA	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat dissipation	2...3 W 50/60 Hz
Operating time	12...22 ms closing 4...19 ms opening
Mechanical durability	10 Mcycles
Maximum operating rate	3600 Cyc/H 140 °F (60 °C)
Auxiliary contacts type	Mechanically linked 1 NO IEC 60947-5-1
Minimum switching current	5 MA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Insulation resistance	> 10 MOhm for signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 Ms on energisation between NC and NO contact
Signalling circuit frequency	25...400 Hz

Connections - terminals	<p>Power circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end</p> <p>Power circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end</p> <p>Power circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible with cable end</p> <p>Power circuit: screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) - cable stiffness: flexible with cable end</p> <p>Power circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: solid without cable end</p> <p>Power circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: solid without cable end</p> <p>Control circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end</p> <p>Control circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end</p> <p>Control circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible with cable end</p> <p>Control circuit: screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) - cable stiffness: flexible with cable end</p> <p>Control circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: solid without cable end</p> <p>Control circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: solid without cable end</p>
Tightening torque	<p>Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm</p> <p>Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2</p> <p>Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm</p> <p>Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals Philips No 2</p>
Mounting Support	Rail Plate
Height	3.35 In (85 mm)
Width	1.77 In (45 mm)
Depth	3.62 In (92 mm)
Net Weight	0.83 Lb(US) (0.375 kg)

Environment

[Ui] rated insulation voltage	<p>Power circuit 690 V IEC 60947-4-1</p> <p>Power circuit 600 V CSA</p> <p>Power circuit 600 V UL</p> <p>Signalling circuit 690 V IEC 60947-1</p>
Overvoltage category	III
Pollution degree	3
[Uimp] rated impulse withstand voltage	6 KV IEC 60947
Standards	<p>CSA C22.2 No 14</p> <p>EN 60947-4-1</p> <p>EN 60947-5-1</p> <p>IEC 60947-4-1</p> <p>IEC 60947-5-1</p> <p>UL 60947-4-1</p>
Product Certifications	UL[RETURN]CSA
IP degree of protection	IP20 front face IEC 60529
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Mechanical robustness	<p>Vibrations contactor open 2 Gn, 5...300 Hz)</p> <p>Vibrations contactor closed 4 Gn, 5...300 Hz)</p> <p>Shocks contactor open 10 Gn for 11 ms)</p> <p>Shocks contactor closed 15 Gn for 11 ms)</p>

Ordering and shipping details

Category	US1011322362
Discount Schedule	0113
GTIN	3606481063267
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.20 In (5.59 cm)
Package 1 Width	3.80 In (9.65 cm)
Package 1 Length	4.70 In (11.94 cm)
Package 1 Weight	0.90 Lb(US) (0.41 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Height	5.91 In (15 cm)
Package 2 Width	11.81 In (30 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	14.80 Lb(US) (6.715 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	256
Package 3 Height	303.15 In (770 cm)
Package 3 Width	23.62 In (60 cm)
Package 3 Length	31.50 In (80 cm)
Package 3 Weight	255.60 Lb(US) (115.94 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Product Life Status : **Commercialised**