



## Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

## Main

Rated power in W	900 W
Rated power in VA	1500 VA
Nb of power socket outlets	8 IEC 320 C13 2 IEC Jumpers
Output voltage	230 V
Output voltage	220 V 240 V
Input voltage	220 V 240 V
Input voltage	230 V
Plug standard	IEC 320 C14

## General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No
Provided equipment	USB cable

## Physical

Mounting location	Front
Mounting mode	Not rack-mountable
Mounting preference	No preference
Depth	43.9 Cm
Height	21.9 Cm
Net weight	20.1 Kg
Width	17.1 Cm
Two post mountable	0

USB compatible	Yes
Colour	Black

## Input

Input voltage limits	170...300 V adjustable 180...287 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1500 VA
Maximum configurable power in W	900 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product certifications	C-Tick CE GOST VDE
Standards	UL 1778

## Environmental

Acoustic level	45 dBA
Heat dissipation	135 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Battery type	Lead-acid battery
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAH	288 VAh runtime
Battery charger power	96 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Free slots	0

## Surge Protection and Filtering

Surge energy rate	459 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Package 1 Weight	22.64 Kg
Package 1 Height	33 Cm
Package 1 width	33 Cm
Package 1 Length	59 Cm
Number of Units in Package 2	1
Number of Units in Package 3	18

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**