



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Rated power in W	1000 W
Rated power in VA	1500 VA
Nb of power socket outlets	4 IEC 320 C13 2 IEC Jumpers C13
Output voltage	230 V
Output voltage	220 V 240 V
Input voltage	220 V 240 V
Input voltage	230 V
Plug standard	IEC 320 C14
Number of rack unit	2U

General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No
Provided equipment	Installation guide Rack mounting support rails USB cable

Physical

Mounting location	Front
Mounting mode	Rack-mounted
Mounting preference	Lower
Depth	47.7 Cm
Height	8.6 Cm
Net weight	26.1 Kg

Width	43.2 Cm
Two post mountable	0
USB compatible	Yes
Colour	Black

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1500 VA
Maximum configurable power in W	1000 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE EAC RCM TÜV VDE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Acoustic level	46 dBA
Heat dissipation	90 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery type	Lead-acid battery
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAH	432 VAh runtime
Battery charger power	144 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Optional
Free slots	1

Surge Protection and Filtering

Surge energy rate	459 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	31.91 Kg
Package 1 Height	25.1 Cm
Package 1 width	59.4 Cm
Package 1 Length	60.3 Cm
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**