



## Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

## General

Provided equipment	Documentation CD Rack mounting hardware Rack mounting support rails USB cable
Additional specification	Cloud-enabled monitoring
Number of tare power	52 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

## Physical

Cable length	2.00 M
Number of rack unit	2U
Depth	68.3 Cm
Height	8.6 Cm
Mounting location	Front
Mounting preference	No preference
Product weight	42.31 Kg
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	No
Width	43.2 Cm

## Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	BS1363A British IEC 320 C20 Schuko CEE 7 / EU1-16P
Input voltage limits	151...302 V adjustable 160...286 V
Inputvolt_other	220 V 240 V
Number of cables	1
Input voltage	230 V

## Output

Rated power in W	1980 W
Maximum configurable power in W	1980 W
Harmonic distortion	Less than 5 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Output voltage	220 V 240 V
UPS type	Line interactive
Wave type	Sine wave
Nb of power socket outlets	8 IEC 320 C13 3 IEC Jumpers 1 IEC 320 C19
Output voltage	230 V
Maximum configurable power in VA	2200 VA
Rated power in VA	2200 VA
Transfer time	6 ms typical : 10 ms maximum

## Conformance

Product certifications	CE EAC IRAM RCM VDE
Marking	GS Mark
Standards	EN 60950 EN/IEC 62040-1 EN/IEC 62040-2

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 M
Acoustic level	55 dBA
Heat dissipation	215 Btu/H

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Liquid value	0

Battery charger power	169 W rated
Battery power in VAh	509 VAh runtime
Battery life	3...5 Year(S)
Extended runtime	0

### Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

### Surge Protection and Filtering

Surge energy rate	375 J
-------------------	-------

### Packing Units

Package 1 Weight	49.73 Kg
Package 1 Height	25.4 Cm
Package 1 width	60 Cm
Package 1 Length	98 Cm
Number of Units in Package 3	8

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

### Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**