

A

B

C




D

A


B

C

D





Electronic controller
in the enclosure side



Includes aluminium filter

NO POPNUTS IN THE
CABINET FRONT FACE




COMMERCIAL REFERENCE	WEIGHT
NSYCUHD1K6DG	39 kg
NSYCUHD1K62P4DG	44.5 kg
NSYCUHD2K3P4DG	42.4 kg

	Scale: 0.125 Technical Specification: ISO 2768-mK Units of measure: mm
	Document Description: CONNECT OUTDOOR CU SIDE 1K6W 2KW Document Number: GEX8223102 Doc. Rev. 00 Sheet: 1/2


The information is highly confidential and is the exclusive property of Schneider Electric copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing. This drawing must be returned to the owners when the purpose has ceased.

Released for Manufacturing
Printed on 2024/06/12

FIXING POINTS



CUT OUT



	Scale: 0.150	Technical Specification: ISO 2768-mK	Units of measure : mm
		Document Description: CONNECT OUTDOOR CU SIDE 1K6W 2KW	
		Document Number: GEX8223102	Doc. Rev. Sheet: 00 2/2

The information is highly confidential and is the exclusive property of Schneider Electric copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing. This drawing must be returned to the owners when the purpose has ceased.

Released for Manufacturing
Printed on 2024/06/12