



Overview

Model Name	APC Easy UPS On-Line SRV RM 6000 VA 230V with Rail Kit
Includes	CD with software , Rack Mounting support rails , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Argentina , Armenia , Austria , Azerbaijan , Belarus , Benin , Bosnia And Herzegovina , Botswana , Bulgaria , Croatia , Cyprus , Czech Republic , Denmark , Estonia , Finland , France , Germany , Greece , French Guiana , Hungary , Iceland , Israel , Italy , Kazakhstan , Latvia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malaysia , Malta , Mauritius , Moldova , Republic Of , Mongolia , Netherlands , Norway , Oman , Pakistan , Paraguay , Philippines , Poland , Portugal , Romania , Russian Federation , Singapore , Slovakia (Slovak Republic) , Slovenia , South Africa , Spain , Sweden , Switzerland , Ukraine , Uruguay , Uzbekistan , Viet Nam , Zambia

Output

Output Power Capacity	6000 Watts / 6000 VA
Max Configurable Power (Watts)	6000 Watts / 6000 VA
Nominal Output Voltage	230V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	220, 240V
Crest Factor	3 : 1
	Double Conversion Online
Waveform Type	Sine wave

Input

Nominal Input Voltage	230V
Input Frequency	40 - 70 Hz
Input Connections	Hard Wire 3-wire
Other Input Voltages	220 , 240

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

Surge Protection and Filtering

Surge energy rating	600 joules
---------------------	------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Maximum Height	173.0 mm
Maximum Width	438.0 mm
Maximum Depth	710.0 mm
Net Weight	61.0 kg

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-14763.6 meters
Audible noise at 1 meter from surface of unit	0.000 dB

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs
REACH SVHC	Lead, CAS#7439-92-1 30% , SVHC-191